
G9EC-1-B-AQ

DC Power Relay (200A type)

Capable of Interrupting Highvoltage, High-current Loads

- A compact relay (L98 x W44x H86.7mm) capable of switching DC400V, 200A. (Capable of interrupting max. DC400V, 1,000A)
- The switching section and driving section are gas-injected and hermetically sealed, allowing these compact relays to interrupt high-current.
 The sealed construction also achieves no arc space, space saving, and helps to ensure safe applications. In addition, the contacts have a high contact reliability that is unaffected by ambient atmosphere.
- Downsizing of parts and optimum design allow no restrictions on the mounting direction.



■ Type standard



	Classification	Symbol	Symbol Meaning of the symbol
1	Number of contact poles	1	1 pole
2	Contact structure	Blank	1a contact
(3)	Coil terminal form	В	M3.5 screw terminal
9	Conteminarionii	Blank	Lead wires
4	Automotive use	AQ	Available for automotive use

■ Classification

Classification	Terminal form		Contact structure	Rated coil voltage	Tuno nomo
Classification	Coil terminals	Contact terminals	Contact structure	nated coil voltage	Type name
Switching / current	Screw terminals	Screw terminals	10	DC12V DC24V	G9EC-1-B-AQ
conduction type	Lead wires	Screw terminals	1a		G9EC-1-AQ

- Note:1. Come with two M8 nuts for main terminals (contacts).
 - 2. Come with two M3.5 screws for screw-type coil terminal products.
 - 3. If you are interested in a connector joint for coil terminal, please contact our sales representatives.

■ Ratings

Operation coil

Rated voltage (V)	Rated current (mA)	Coil resistance (Ω)	Operating voltage (V)	Release voltage (V)	Maximum voltage (V)	Power consumption (W)
DC 12	583	20.6	750/	00/	130% of rated	
DC 24	292	82.3	75% or less of rated voltage	8% or more of rated voltage	voltage (at 23°C within 10min.)	Approx. 7

- Note:1. Values of the rated current and the coil resistance are at coil temperature of +23°C, and have a tolerance of ±10%.
 - 2. The figures for the operating characteristics are at a coil temperature of 23°C.
 - 3. Value of the maximum voltage is the maximum voltage that can be applied to the relay coil.

Switching area

Item	Resistance load	
	G9EC-1(-B)-AQ	
Rated load	DC400V 200A	
Rated current	200A	
Maximum switching voltage	400V	
Maximum switching current	200A	


Performance

Item		G9EC-1(-B)-AQ	
Contact resistance *	1	30 mΩ or less (Typ. 0.2mΩ)	
Contact voltage drop	0	0.1V or less (at 200A)	
Operating time		50 ms or less	
Release time		30 ms or less	
Insulation	Between coil and contacts	1,000 M Ω or more	
resistance*2	Between homopolar contacts	1,000 M Ω or more	
Withstand voltage	Between coil and contacts	AC2,500V for 1min.	
willistand voitage	Between homopolar contacts	AC2,500V for 1min.	
Vibration tolerance	Durability	5 to 200 to 5Hz Single amplitude 0.75mm (Acceleration: 2.94 to 88.9m/s²)	
Vibration tolerance	Malfunction	5 to 200 to 5Hz Single amplitude 0.75mm (Acceleration: 2.94 to 88.9m/s²)	
Shock resistance	Durability	490 m/s ²	
SHOCK resistance	Malfunction	200 m/s ²	
Mechanical endurance *3		200,000 times or more	
Electrical endurance (Resistance load) *4		DC400V 200A 3,000 times or more	
Short time carry current		300A (for 15 min)	
Maximum interruption	on current	DC400V 1,000A (10 times)	
Overload interruption		DC400V 700A (40 times or more)	
Reverse polarity interruption		DC200V –200A (1,000 times or more)	
Minimum load current		1A	
Ambient temperature		-40 to +85°C (with no icing or condensation)	
Ambient humidity		5% to 85%RH	
Weight (including accessories)		Approx. 650g	


Note: All values above are in early time under an ambient temperature of +23°C unless stated.


- *1. Measurement condition: By voltage drop method at DC5V 1A.
 *2. Measurement condition: By insulation resistance at DC500V.
- *3. Test condition / Switching frequency: 3,600 times/hour.
 *4. Test condition / Switching frequency: 60 times/hour.

■ Dimensions (Unit: mm)












Note: Be sure to connect terminals with the correct polarity. Coils do not have polarity.

Size (mm)	Tolerance (mm)
to 10	±0.3
10 to 50	±0.5
50 to	±1









●Relay with Lead Wires G9EC-1-AQ


Size






Size (mm)	Tolerance (mm)
to 10	±0.3
10 to 50	±0.5
50 to	±1








Note: Be sure to connect terminals with the correct polarity. Coils do not have polarity.

Mounting holes (BOTTOM VIEW)



32±0.1