D6F-N2/-L2

MEMS Flow Sensor

A Compact, High-accuracy Sensor That Measures Low Flow Rates.

- High accuracy of ±3% FS.
- Flow rates can be measured without being affected by temperature or pressure.

RoHS Compliant



Refer to the Common Precautions for the D6F Series on page 40. on page 40.

Ordering Information

MEMS Flow Sensor

Applicable fluid	Flow rate range	Model
Natural gas (13A)	0 to 1 L/min	D6F-01N2-000
	0 to 5 L/min	D6F-05N2-000
LP gas	0 to 2 L/min	D6F-02L2-000

Accessory (included)

Туре	Model		
Cable	D6F-CABLE1		

Connections


D6F-01N2-000 D6F-05N2-000 D6F-02L2-000

2: Vout 3: GND

53398-03** (Made by Molex Japan) Connector

Use the following connectors for connections to the D6F: Housing 51021-0300 (Made by Molex Japan) 50079 (Made by Molex Japan) Terminals

AWG28 to AWG26 Wires








Output Voltage Characteristics


D6F-01N2-000

5.0 voltage (V) 4.0 3.0 2.0 1.0

D6F-05N2-000



D6F-02L2-000



D6F-01N2-000

Flow rate L/min (normal)	0	0.2	0.4	0.6	0.8	1.0
Output voltage	1.00	1.90	2.81	3.64	4.37	5.00
V	±0.12	±0.12	±0.12	±0.12	±0.12	±0.12

D6F-05N2-000

Flow rate L/min (normal)	0	1.0	2.0	3.0	4.0	5.0
Output voltage	1.00	2.91	3.92	4.47	4.79	5.00
V	±0.12	±0.12	±0.12	±0.12	±0.12	±0.12

D6F-02L2-000

Flow rate L/min (normal)	0	0.4	0.8	1.2	1.6	2.0
Output voltage	1.00	3.02	3.95	4.47	4.79	5.00
V	±0.30	±0.08	±0.08	±0.08	±0.08	±0.12

Measurement conditions: Power supply voltage of 12±0.1 VDC, ambient temperature of 25±5°C, and ambient humidity of 35% to 75%.

Characteristics/Performance

Model	D6F-01N2-000	D6F-05N2-000	D6F-02L2-000		
Flow Range (See note 1.)	0 to 1 L/min	0 to 5 L/min	0 to 2 L/min.		
Calibration Gas (See note 2.)	Natural gas (13A) Propane gas				
Flow Port Type	Rc 1/4 thread	Rc 1/4 thread			
Electrical Connection	Three-pin connector				
Power Supply	10.8 to 26.4 VDC				
Current Consumption	15 mA max. with no load, with a Vcc of	12 to 24 VDC, and at 25°C			
Output Voltage	1 to 5 VDC (non-linear output, load resis	stance of 10 kΩ)			
Accuracy	±3% FS (25°C characteristic)		±2% to ±7.5% F.S. (25°C		
Accuracy	15% 13 (25 C characteristic)		characteristic)		
Repeatability (See note 3.)	±0.2% FS	±0.2% FS ±0.3% FS			
Output Voltage (Max.)	5.7 VDC (Load resistance: 10 kΩ)				
Output Voltage (Min.)	0 VDC (Load resistance: 10 kΩ)				
Rated Power Supply Voltage	26.4 VDC				
Rated Output Voltage	6 VDC				
Case	Aluminum alloy				
Degree of Protection	IEC IP40 (Excluding tubing sections.)				
Withstand Pressure	200 kPa				
Pressure Drop (See note 3.)	0.017 kPa	0.10 kPa	0.14 kPa		
Operating Temperature (See note 4.)	-10 to 60°C				
Operating Humidity (See note 4.)	35% to 85%				
Storage Temperature (See note 4.)	−40 to 80°C				
Storage Humidity (See note 4.)	35% to 85%				
Temperature Characteristics	±3% FS for 25°C characteristic at -10 to 60°C		±4% FS for 25°C characteristic at –10 to 60°C		
Insulation Resistance	Between Sensor outer cover and lead terminals: 20 MΩ min. (at 500 VDC)				
Dielectric Strength	Between Sensor outer cover and lead terminals: 500 VAC, 50/60 Hz min. for 1 min (leakage current: 1 mA max.)				
Weight	35.3 g				

Note: 1. Volumetric flow rate at 0°C, 101.3 kPa.


Note: 2. Dry gas. (must not contain large particles, e.g., dust, oil, or mist.)

Note: 3. Reference (typical)


Note: 4. With no condensation or icing.

Dimensions (Unit: mm)

D6F-01N2-000 D6F-05N2-000 D6F-02L2-000



Mounting Hole Dimensions



Cable (included): D6F-CABLE1

