OMRON Piano DIP Switch

A6HR

Piano DIP Switches with Half-pitch

- Gold-plated twin contacts ensure high reliability.
- Embossed taping are available for small-reel 100 pcs/500 pcs.

RoHS Compliant



■ List of Models


Туре	Standard									
	Tube packaging		Embossed taping							
			Standard reel		Small reel					
	LITT THE FUTURE FUTURE									
	Quantity per	Tube	Quantity per	Embossed taping	Quantity	Embossed taping	Quantity per	Embossed taping		
No. of poles	tube	packaging	reel	Standard reel	per reel	Small reel	reel	100 pcs reel		
2	125	A6HR-2104	1,000	A6HR-2104- P	500	A6HR-2104- PM	100	A6HR-2104- R100		
4	70	A6HR-4104		A6HR-4104- P		A6HR-4104- PM		A6HR-4104- R100		
6	50	A6HR-6104		A6HR-6104- P		A6HR-6104- PM		A6HR-6104- R100		
8	40	A6HR-8104		A6HR-8104- P		A6HR-8104- PM		A6HR-8104- R100		
10	30	A6HR-0104		A6HR-0104- P		A6HR-0104- PM		A6HR-0104- R100		

Note: Order in multiples of the package quantity.

Ratings/Characteristics

Rating (resistive load)		25 mA at 24 VDC 10 μA (minimum current) at 3.5 VDC				
Ambient operating ten	nperature	-30 to +85 °C at 60% max. (with no icing or condensation)				
Ambient operating hui	nidity	35% to 95% (at +5 to +35 °C)				
Insulation resistance		100 M Ω min. (at 100 VDC with insulation tester)				
Contact resistance (initial value)		200 mΩ max.				
Dielectric strength	Between terminals	300 VAC for 1 min				
Vibration resistance	Malfunction	10 to 55 Hz, 1.5-mm double amplitude				
Shock resistance	Malfunction	490 m/s ² min.				
Durability	Electrical	1,000 operations min.				
Washing		Not possible				
Degree of protection		IEC IP40				
Operating force (OFF t	to ON)	0.29 to 4.9 N {30 to 500 gf}				
Weight		0.13g (2 poles) 0.22g (4 poles) 0.3g (6 poles) 0.4g (8 poles) 0.48g (10 poles)				


■ **Dimensions** (Unit: mm)



Note: Unless otherwise specified, a tolerance of ±0.4 mm applies to all dimensions.

Internal Connections

Contact Form (Top View)



Precautions

Be sure to read the Safety precautions common to all DIP Switches for correct use.

Application examples provided in this document are for reference only. In actual applications, confirm equipment functions and safety before using the product.
Consult your OMRON representative before using the product under conditions which are not described in the manual or applying the product to nuclear control systems, railroad systems, aviation systems, vehicles, combustion systems, medical equipment, amusement machines, safety equipment, and other systems or equipment that may have a serious influence on lives and property if used improperty. Make sure that the ratings and performance characteristics of the product provide a margin of safety for the system or equipment, and be sure to provide the system or equipment with double safety mechanisms.

Note: Do not use this document to operate the Unit.

OMRON Corporation

Electronic and Mechanical Components Company

Contact: www.omron.com/ecb

Cat. No. A191-E1-07 0619(0207)(O)