

MOS FET Relays

G3VM-355J/JR

New MOS FET Relays with Both SPST-NO and SPST-NC Contacts Incorporated in a Single SOP Package.

General-purpose Models Added.

- SPST-NO/SPST-NC models with an 8-pin SOP package now available in the 350-V load voltage series.
- Continuous load current of 120 mA (90 mA).
- Dielectric strength of 1,500 Vrms between I/O.
- General-purpose models (models with high ON resistance) added to the series.



Note: The actual product is marked differently from the image shown here.

RoHS compliant

Refer to "Common Precautions".

Application Examples

- Broadband systems
- Measurement devices
- Data loggers
- Amusement machines


List of Models

Contact form	Terminals	Load voltage (peak value)	Model	Number per stick	Number per tape
SPST-NO/ SPST-NC	Surface-mounting terminals	350 VAC	G3VM-355JR	50	---
			G3VM-355J		
			G3VM-355JR(TR)	---	2,500
			G3VM-355J(TR)		


Dimensions

Note: All units are in millimeters unless otherwise indicated.

G3VM-355J/JR




Note: The actual product is marked differently from the image shown here.




Terminal Arrangement/Internal Connections (Top View)

G3VM-355J/JR



Actual Mounting Pad Dimensions (Recommended Value, Top View)

G3VM-355J/JR



Absolute Maximum Ratings (Ta = 25°C)

Item	Symbol	Rating	Unit	Measurement Conditions	
Input	LED forward current	I_F	50	mA	
	Repetitive peak LED forward current	I_{FP}	1	A	100 μ s pulses, 100 pps
	LED forward current reduction rate	$\Delta I_F/^\circ\text{C}$	-0.5	mA/°C	Ta \geq 25°C
	LED reverse voltage	V_R	5	V	
	Connection temperature	T_j	125	°C	
Output	Output dielectric strength	V_{OFF}	350	V	
	Continuous load current	I_O	120 (90)	mA	
	ON current reduction rate	$\Delta I_{ON}/^\circ\text{C}$	-1.2 (-0.9)	mA/°C	Ta \geq 25°C
	Connection temperature	T_j	125	°C	
Dielectric strength between input and output (See note 1.)		V_{I-O}	1,500	Vrms	AC for 1 min
Operating temperature		T_a	-40 to +85	°C	With no icing or condensation
Storage temperature		T_{stg}	-55 to +125	°C	With no icing or condensation
Soldering temperature (10 s)		---	260	°C	10 s


Note: 1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

Values in parentheses are for the G3VM-355J.

Electrical Characteristics (Ta = 25°C)

Item	Symbol	Minimum	Typical	Maximum	Unit	Measurement conditions	
Input	LED forward voltage	V_F	1.0	1.15	1.3	V	$I_F = 10$ mA
	Reverse current	I_R	---	---	10	μ A	$V_R = 5$ V
	Capacity between terminals	C_T	---	30	---	pF	V = 0, f = 1 MHz
	Trigger LED forward current	I_{FT}	---	1	3	mA	SPST-NO: $I_O = 90$ mA
I_{FC}		---	---	---	---	SPST-NC: $I_{OFF} = 10$ μ A	
Output	Maximum resistance with output ON	R_{ON}	---	15 (40)	25 (50)	Ω	SPST-NO: $I_F = 5$ mA, $I_O = 90$ mA SPST-NC: $I_F = 0$ mA, $I_O = 90$ mA
		Current leakage when the relay is open	I_{LEAK}	---	---	1.0	μ A
Capacity between I/O terminals		C_{I-O}	---	0.8	---	pF	f = 1 MHz, Vs = 0 V
Insulation resistance		R_{I-O}	1,000	---	---	M Ω	$V_{I-O} = 500$ VDC, RoH \leq 60%
Turn-ON time	SPST-NO	t_{ON}	---	(0.3)	1.0	ms	$I_F = 5$ mA, $R_L = 200$ Ω , $V_{DD} = 20$ V (See note 2.)
	SPST-NC	---	---	(0.25)	1.0	ms	
Turn-OFF time	SPST-NO	t_{OFF}	---	(0.15)	1.0	ms	
	SPST-NC	---	---	(0.5)	3.0 (1)	ms	

Note: 2. Turn-ON and Turn-OFF Times



Values in parentheses are for the G3VM-355J.

Recommended Operating Conditions

Use the G3VM under the following conditions so that the Relay will operate properly.


Item	Symbol	Minimum	Typical	Maximum	Unit
Output dielectric strength	V_{DD}	---	---	280	V
Operating LED forward current	I_F	5	---	25	mA
Continuous load current	I_O	---	---	120 (90)	mA
Operating temperature	T_a	-20	---	65	°C

Values in parentheses are for the G3VM-355J.

Engineering Data

Load Current vs. Ambient Temperature

G3VM-355J/JR



Safety Precautions

Refer to "Common Precautions" for all G3VM models.