




## PCB-mounting SSR for FA Equipment Requiring High Reliability

- 3 to 28 VDC input and 75 to 264 VAC output.
- Wide I/O voltage range: 3 to 28 VDC input and 3 to 52.8 VDC output.
- Two load currents available: 2 A and 3 A
- Flat and vertical models available for a variety of applications.
- Lineup includes models with UL and CSA certification (model numbers ending in “-US”).



**RoHS Compliant**

Refer to "Solid State Relays Common Precautions".

### List of Models

Isolation	Zero cross function	Indicator	Rated output load	Rated input voltage	Model	Minimum packing unit
Photocoupler	Yes		2 A at 100 to 240 VAC	4 to 24 VDC	<b>G3CN-202P</b>	10 pcs
					<b>G3CN-202P1 *1</b>	20 pcs
			3 A at 100 to 240 VAC		<b>G3CN-203P</b>	10 pcs
					<b>G3CN-203P1 *1</b>	20 pcs
Phototriac	No	No	2 A at 100 to 240 VAC	5 VDC 12 VDC 24 VDC *2	<b>G3CN-202PL</b>	10 pcs
					<b>G3CN-202PL1 *1</b>	20 pcs
			3 A at 100 to 240 VAC		<b>G3CN-203PL</b>	10 pcs
					<b>G3CN-203PL1 *1</b>	20 pcs
Photocoupler	-		2 A at 4 to 48 VDC	4 to 24 VDC	<b>G3CN-DX02P</b>	10 pcs
					<b>G3CN-DX02P1 *1</b>	20 pcs
			3 A at 4 to 48 VDC		<b>G3CN-DX03P</b>	10 pcs
					<b>G3CN-DX03P1 *1</b>	20 pcs

\*1. These are vertical types. \*2 When ordering, specify the input voltage.

### Ratings

#### Input

Model	Item	Rated voltage	Operating voltage	Input impedance	Voltage level	
					Must operate voltage	Must release voltage
G3CN-202P(1) G3CN-203P(1)		4 to 24 VDC	3 to 28 VDC	1.5 kΩ +20%/-10%	3 VDC max.	1 VDC min.
G3CN-202PL(1) G3CN-203PL(1)		5 VDC	4 to 6 VDC	390 Ω ±20%	4 VDC max.	
		12 VDC	9.6 to 14.4 VDC	900 Ω ±20%	9.6 VDC max.	
		24 VDC	19.2 to 28.8 VDC	2 kΩ ±20%	19.2 VDC max.	
G3CN-DX02P(1) G3CN-DX03P(1)		4 to 24 VDC	3 to 28 VDC	1.5 kΩ +20%/-10%	3 VDC max.	

#### Output

Model	Item	Applicable load			
		Rated load voltage	Load voltage range	Load current	Inrush current
G3CN-202P(1) G3CN-202PL(1)		100 to 240 VAC	75 to 264 VAC	0.1 to 2 A *	30 A (60 Hz, 1 cycle)
				0.1 to 3 A *	45 A (60 Hz, 1 cycle)
G3CN-203P(1) G3CN-203PL(1)		4 to 48 VDC	3 to 52.8 VDC	0.1 to 2 A *	12 A (10 ms)
				0.1 to 3 A *	18 A (10 ms)

Note. The input impedance values are the maximum values of applied voltage. (measured at 28 VDC for 4 to 24 VDC models)


\* The load current varies depending on the ambient temperature. Refer to Load Current vs. Ambient Temperature under Engineering Data.

### Characteristics

Model	Item	G3CN-202P(1), G3CN-203P(1)	G3CN-202PL(1), G3CN-203PL(1)	G3CN-DX02P(1), G3CN-DX03P(1)
Operate time		1/2 of load power source cycle + 1 ms max.	1 ms max.	0.5 ms max.
Release time		1/2 of load power source cycle + 1 ms max.	1/2 of load power source cycle + 1 ms max.	2 ms max.
Output ON voltage drop		1.6 V (RMS) max.		1.5 V max.
Leakage current		5 mA max. (at 100 VAC) 10 mA max. (at 200 VAC)	2.5 mA max. (at 100 VAC) 5 mA max. (at 200 VAC)	5 mA max. (at 50 VDC)
Insulation resistance		100 MΩ min. (at 500 VDC)		
Dielectric strength		2,500 VAC, 50/60 Hz for 1 min between input and output		
Vibration resistance		10 to 55 to 10 Hz, 0.75-mm single amplitude (1.5-mm double amplitude)		
Shock resistance		1,000 m/s <sup>2</sup>		
Ambient Operating temperature		-30°C to 80°C (with no icing nor condensation)		
Ambient Operating humidity		45% to 85%RH		
Storage Temperature		-30°C to 100°C (with no icing nor condensation)		
Weight		Approx. 25 g		

## Engineering Data


### Load Current vs. Ambient Temperature Characteristics G3CN-202P(1), G3CN-202PL(1), G3CN-DX02P(1)




### One Cycle Surge Current: Non-repetitive

Non-repetitive (Keep the inrush current to half the rated value if it occurs repetitively.)


#### 2-A Load Model G3CN-202P(1), G3CN-202PL(1)




#### G3CN-DX02P(1)




### G3CN-203P(1), G3CN-203PL(1), G3CN-DX03P(1)



#### 3-A Load Model G3CN-203P(1), G3CN-203PL(1)



#### G3CN-DX03P(1)





## Dimensions


(Unit: mm)

### Flat Model


G3CN-20□P  
G3CN-20□PL  
G3CN-DX0□P



**Mounting Holes**  
Tolerance:  $\pm 0.1$  mm unless specified  
(BOTTOM VIEW)





**Terminal Arrangement/  
Internal Connections**  
(BOTTOM VIEW)




Note. The plus and minus symbols shown in the parentheses are for DC loads.

### Vertical Model


G3CN-20□P1  
G3CN-20□PL1  
G3CN-DX0□P1



**Mounting Holes**  
Tolerance:  $\pm 0.1$  mm unless specified  
(BOTTOM VIEW)



**Terminal Arrangement/  
Internal Connections**  
(BOTTOM VIEW)



Note. The plus and minus symbols shown in the parentheses are for DC loads.

## Precautions

● Please refer to "Solid State Relays Common Precautions" for correct use.

- Application examples provided in this document are for reference only. In actual applications, confirm equipment functions and safety before using the product.
- Consult your OMRON representative before using the product under conditions which are not described in the manual or applying the product to nuclear control systems, railroad systems, aviation systems, vehicles, combustion systems, medical equipment, amusement machines, safety equipment, and other systems or equipment that may have a serious influence on lives and property if used improperly. Make sure that the ratings and performance characteristics of the product provide a margin of safety for the system or equipment, and be sure to provide the system or equipment with double safety mechanisms.

**Note: Do not use this document to operate the Unit.**