G3VM-61G1 MOS FET Relays

MOS FET Relays Designed for Switching Minute Signals and Analog Signals.

• Upgraded G3VM-S1 Series.

• Continuous load current of 400 mA.

RoHS compliant

Application Examples


- Semiconductor test equipment
- Test & Measurement equipment
- Communication equipment
- Data loggers



71

Note: The actual product is marked differently from the image shown here.

Terminal Arrangement/Internal Connections



Note: The actual product is marked differently from the image shown here. * The indentation in the corner diagonally opposite from the pin 1 mark is from a pin on the mold.

■ List of Models

Package type	Contact form	Terminals	Load voltage	Model	Minimum pac	kage quantity
Fackage type	Contact Ionni	renninais	(peak value) *	Model	Number per tube	Number per tape and reel
SOP4	1a	Surface-mounting Terminals	60 V	G3VM-61G1	100	-
30F4	(SPST-NO)	Sunace-mounting reminals	00 V	G3VM-61G1 (TR)	-	2,500


* The AC peak and DC value are given for the load voltage.


■ Absolute Maximum Ratings (Ta = 25°C)

	Item	Symbol	Rating	Unit	Measurement conditions														
	LED forward current	IF	50	mA															
out	LED forward current reduction rate	∆IF/°C	-0.5	mA/°C	Ta ≥ 25°C														
du	LED reverse voltage	VR	5	V															
	Connection temperature	TJ	125	°C															
	Load voltage (AC peak/DC)	Voff	60	V															
put	Continuous load current (AC peak/DC)	lo	400	mA															
ort	ON current reduction rate	∆lo/°C	-4.0	mA/°C	Ta ≥ 25°C														
	Connection temperature	TJ	125	°C															
	ectric strength between See note 1.)	VI-0	1500	Vrms	AC for 1 min	Note: 1	The di	ماد	ntric st	ctric strength	ctric strength betwe	ctric strength between the	stric strength between the inn	ctric strength between the input	stric strength between the input a	ctric strength between the input a	stric strength between the input an	ctric strength between the input and	stric strength between the input and
Amb	ient operating temperature	Та	-40 to +85	°C	With no icing or condensation	11010.1					0	0	5	s checked by applying voltage	5	5	5 1	5 1	5
Amb	ent storage temperature	Tstg	-55 to +125	°C	With no icing or condensation														Il pins as a group on the LED side and
Solo	dering temperature	-	260	°C	10 s		all pins	as	a gro	a group on	a group on the ligh	a group on the light-rece	a group on the light-receiving	a group on the light-receiving s	a group on the light-receiving sid	a group on the light-receiving sid	a group on the light-receiving side	a group on the light-receiving side.	a group on the light-receiving side.

Electrical Characteristics (Ta = 25°C)

	Item	Symbol	Minimum	Typical	Maximum	Unit	Measurement conditions
	LED forward voltage	VF	1.0	1.15	1.3	V	IF = 10 mA
out	Reverse current	IR	-	-	10	μA	VR = 5 V
Inp	Capacity between terminals	Ст	-	30	-	pF	V = 0, f = 1 MHz
	Trigger LED forward current	IFT	-	1.6	3	mA	lo = 400 mA
ut	Maximum resistance with output ON	Ron	-	1	2	Ω	IF = 5 mA, Io = 400 mA
utp	Current leakage when the relay is open	ILEAK	-	-	1.0	μA	Voff = 60 V
õ	Capacity between terminals	Coff	-	130	-	pF	V = 0, f = 1 MHz
Capacity between I/O terminals		CI-O	-	0.8	-	pF	f = 1 MHz, Vs = 0 V
Insulation resistance between I/O terminals		Rı-o	1000	-	-	MΩ	VI-0 = 500 VDC, RoH \leq 60 %
Tur	n-ON time	ton	-	0.8	2.0	ms	$IF = 5 \ mA, \ RL = 200 \ \Omega,$
Tur	n-OFF time	toff	-	0.1	0.5	ms	VDD = 20 V (See note 2.)





G3VM-61G1


Recommended Operating Conditions

Use the G3VM under the following conditions so that the Relay will operate properly.


Item	Symbol	Minimum	Typical	Maximum	Unit
Load voltage (AC peak/DC)	Vdd	-	-	48	V
Operating LED forward current	lF	5	7.5	25	mA
Continuous load current (AC peak/DC)	lo	-	-	400	mA
Ambient operating temperature	Та	-20	-	65	°C

Engineering Data


LED forward current vs. Ambient temperature




Continuous load current vs. Ambient temperature




LED forward current vs. LED forward voltage




Continuous load current vs. On-state voltage




Turn ON, Turn OFF time vs. LED forward current




On-state resistance vs. Ambient temperature




Turn ON, Turn OFF time vs. Ambient temperature



Trigger LED forward current vs. Ambient temperature



Current leakage vs. Ambient temperature




■ Safety Precautions

• Refer to "Common Precautions" for all G3VM models.

■ Appearance








Note: The actual product is marked differently from the image shown here. * The indentation in the corner diagonally opposite from the pin 1 mark is from a pin on the mold.

Dimensions

(Unit: mm)



Application examples provided in this document are for reference only. In actual applications, confirm equipment functions and safety before using the product.
Consult your OMRON representative before using the product under conditions which are not described in the manual or applying the product to nuclear control systems, railroad systems, aviation systems, vehicles, combustion systems, medical equipment, amusement machines, safety equipment, and other systems or equipment that may have a serious influence on lives and property if used improperty. Make sure that the ratings and performance characteristics of the product provide a margin of safety for the system or equipment with double safety mechanisms.

Note: Do not use this document to operate the Unit.

OMRON Corporation ELECTRONIC AND MECHANICAL COMPONENTS COMPANY Co

Contact: www.omron.com/ecb

Cat. No. K152-E1-01 0412(0412)(O)