


# A High-capacity, High-dielectric-strength Relay Compatible with Momentary Voltage Drops

- No contact chattering for momentary voltage drops up to 50% of rated voltage.
- Wide-range AC-activated coil that handles 100 to 120 or 200 to 240 VAC at either 50 or 60 Hz.
- Miniature size for maximum switching power, particularly for inductive loads
- Flame-resistance materials (UL94V-0-qualifying) used for all insulation material.
- Quick-connect, screw, and PCB terminals, and DIN track mounting available.
- Conforms to UL, CSA, TUV and meets IEC950.
- Safety design with contact gap of 3 mm.

**RoHS Compliant** 



Note. Accessories: E-bracket, Adapter, Front-connecting socket and Cover sold separately.

# **■**Model Number Legend

1. Number of Poles 3. Terminal Shape

1: 1 pole

2: 2 poles
2. Contact Form

A: PST-NO

T: Quick connect

terminals (#250)

B: Screw terminals

P: PCB terminals

4. Mounting Construction

Blank: E-bracket UB: Upper bracket

5. Special Functions
J: With test button

# ■Model Configuration

|                  |           | Terminal     | Quick-connect terminals | Screw terminals | PCB terminals |
|------------------|-----------|--------------|-------------------------|-----------------|---------------|
|                  |           |              |                         |                 | <b>&gt;</b>   |
| Classification   |           | Contact form |                         |                 |               |
| E-bracket        |           | SPST-NO      | G7L-1A-T                | G7L-1A-B        | -             |
| mounting         | _         | DPST-NO      | G7L-2A-T                | G7L-2A-B        | _             |
| (E-bracket is    | With test | SPST-NO      | G7L-1A-TJ               | G7L-1A-BJ       | _             |
| sold separately) | button    | DPST-NO      | G7L-2A-TJ               | G7L-2A-BJ       | _             |
|                  |           | SPST-NO      | G7L-1A-TUB              | G7L-1A-BUB      | _             |
| Upper bracket    | _         | DPST-NO      | G7L-2A-TUB              | G7L-2A-BUB      | _             |
| mounting         | With test | SPST-NO      | G7L-1A-TUBJ             | G7L-1A-BUBJ     | _             |
|                  | button    | DPST-NO      | G7L-2A-TUBJ             | G7L-2A-BUBJ     | -             |
| PCB mounting     |           | SPST-NO      | -                       | -               | G7L-1A-P      |
| rob mounting     | _         | DPST-NO      | -                       | -               | G7L-2A-P      |

# **■**Application Examples

- · Compressors for air conditioners and heater switching controllers.
- Switching controllers for power tools or motors.
- · Power controllers for water heaters.
- · Power controllers for dryers.
- Lamp controls, motor drivers, and power supply switching in copy machines, facsimile machines, and other office equipment.
- · Lighting controllers.
- Power controllers for packers or food processing equipment.
- · Magnetron control in microwaves.
- Power controllers for Uninterruptible Power Supply (UPS)

# **■**List of E-bracket Mounting Models

|           |                 |           | Mounting         | E-brackets | DIN Track<br>Mounting<br>Adapter | Front-connecting<br>Socket |
|-----------|-----------------|-----------|------------------|------------|----------------------------------|----------------------------|
| Terminal  | Contact<br>form | Model     | Test button      |            |                                  |                            |
| Terminal  |                 | G7L-1A-T  | -                | 0          | 0                                | 0                          |
| Quick-    | SPST-NO         | G7L-1A-TJ | With test button | 0          | 0                                | 0                          |
| connect   |                 | G7L-2A-T  | -                | 0          | 0                                | 0                          |
| terminals | DPST-NO         | G7L-2A-TJ | With test button | 0          | 0                                | 0                          |
|           |                 | G7L-1A-B  | -                | 0          | 0                                | _                          |
| Screw     | SPST-NO         | G7L-1A-BJ | With test button | 0          | 0                                | _                          |
| terminals |                 | G7L-2A-B  | -                | 0          | 0                                | _                          |
|           | DPST-NO         | G7L-2A-BJ | With test button | 0          | 0                                | _                          |

Note. Accessories: E-bracket (R99-07), Adapter (P7LF-D), Front-connecting socket (P7LF-06) and Cover (P7LF-C) sold separately.

# **■**Ordering Information

# E-bracket/Adapter/Socket Mounting **Quick-connect Terminal**

| Number of poles | Model    | Rated coil voltage               | Minimum packing unit |
|-----------------|----------|----------------------------------|----------------------|
| 1 pole          | G7L-1A-T | AC: 12, 24, 100/120, 200/240     |                      |
| i pole          | G/L-IA-I | DC: 6, 12, 24, 48, 100           | 20 pcs./tray         |
| 2 poles         | G7L-2A-T | AC: 12, 24, 50, 100/120, 200/240 | 20 pcs./iray         |
| 2 poles         | G/L-2A-1 | DC: 6, 12, 24, 48, 100           |                      |

# **Upper Bracket Mounting Quick-connect Terminal**

| Number of poles | Model      | Rated coil voltage               | Minimum packing unit |
|-----------------|------------|----------------------------------|----------------------|
| 1 pole          | G7L-1A-TUB | AC: 12, 24, 100/120, 200/240     |                      |
|                 | G/L-IA-IOB | DC: 6, 12, 24, 48, 100           | 20 pcs./tray         |
|                 | G7L-2A-TUB | AC: 12, 24, 50, 100/120, 200/240 | ZU pos./liay         |
| 2 poles         | G/L-2A-10B | DC: 6, 12, 24, 48, 100           |                      |

# E-bracket/Adapter Mounting **Screw Terminal**

| Number of poles        | Model    | Rated coil voltage           | Minimum packing unit |
|------------------------|----------|------------------------------|----------------------|
| 1 pole <b>G7L-1A-B</b> |          | AC: 12, 24, 100/120, 200/240 |                      |
| i pole                 | G/L-TA-B | DC: 6, 12, 24, 48, 100       | 20 pcs./tray         |
| 2 poles                | G7L-2A-B | AC: 12, 24, 100/120, 200/240 | – 20 pcs./iray       |
| 2 poles                | G/L-2A-B | DC: 12, 24, 48, 100          |                      |

# **Upper Bracket Mounting Screw Terminal**

| Number of poles   | Model      | Rated coil voltage               | Minimum packing unit |
|-------------------|------------|----------------------------------|----------------------|
| 1 pole G7L-1A-BUB |            | AC: 24, 100/120, 200/240         |                      |
| i pole            | G/L-IA-BOB | DC: 6, 12, 24, 48, 100           | 20 pcs./tray         |
| 2 poles           | G7L-2A-BUB | AC: 12, 24, 50, 100/120, 200/240 | ZU pos./iray         |
| 2 poles           | G/L-ZA-BUB | DC: 6, 12, 24, 48, 100           |                      |

#### **PCB Mounting**

| Number of poles | Model    | Rated coil voltage       | Minimum packing unit |
|-----------------|----------|--------------------------|----------------------|
| 1 pole          | G7L-1A-P | AC: 100/120, 200/240     | 20 pcs./tray         |
| i pole          | G/L-TA-P | DC: 12, 24, 48, 100      |                      |
| 2 poles         | G7L-2A-P | AC: 24, 100/120, 200/240 |                      |
| 2 poles         | G/L-ZA-P | DC: 6, 12, 24, 48, 100   |                      |

# **DIN Track Mounting Accessories**

| Applicable products                  | Name      | Model     | Minimum packing unit |
|--------------------------------------|-----------|-----------|----------------------|
|                                      |           | PFP-100N  |                      |
|                                      | DIN Track | PFP-50N   |                      |
| Adaptor Surface<br>Connection Socket |           | PFP-100N2 | 10 pcs.              |
| Connection Socket                    | End plate | PFP-M     |                      |
|                                      | Spacer    | PFP-S     |                      |

Note. Order the models above in increments of the minimum quantity packaged.

# E-bracket/Adapter/Socket Mounting (with test button) **Quick-connect Terminal**

| Number of poles | Model     | Rated coil voltage       | Minimum packing unit |
|-----------------|-----------|--------------------------|----------------------|
| 1 pole          | G7L-1A-TJ | AC: 24, 100/120, 200/240 | 20 pcs./tray         |
| i pole          | G/L-IA-IJ | DC: 12, 24, 48, 100      |                      |
| 2 poles         | G7L-2A-TJ | AC: 24, 100/120, 200/240 | 20 pcs./tray         |
| 2 poles         | G/L-2A-13 | DC: 6, 12, 24, 48, 100   |                      |

# **Upper Bracket Mounting (with test button) Quick-connect Terminal**

| Number of poles | Model       | Rated coil voltage               | Minimum packing unit |
|-----------------|-------------|----------------------------------|----------------------|
| 1 pole          | G7L-1A-TUBJ | AC: 24, 100/120, 200/240         |                      |
| i pole          | G/L-1A-10B3 | DC: 6, 12, 24, 48, 100           | 20 pcs./tray         |
| 2 poles         | G7L-2A-TUBJ | AC: 12, 24, 50, 100/120, 200/240 | 20 pcs./tray         |
| z poles         | G/L-2A-1000 | DC: 6, 12, 24, 48, 100           |                      |

# E-bracket/Adapter Mounting (with test button) **Screw Terminal**

| Number of poles  | Model      | Rated coil voltage           | Minimum packing unit |
|------------------|------------|------------------------------|----------------------|
| 1 pole           | G7L-1A-BJ  | AC: 12, 24, 100/120, 200/240 |                      |
| i pole G/L-IA-BJ | DC: 12, 24 | 20 pcs./tray                 |                      |
| 2 poles          | G7L-2A-BJ  | AC: 24, 100/120, 200/240     | 20 pcs./ilay         |
| z poles          | G/L-2A-B0  | DC: 12, 24, 48, 100          |                      |

# **Upper Bracket Mounting (with test button) Screw Terminal**

| Number of poles | Model       | Rated coil voltage       | Minimum packing unit |
|-----------------|-------------|--------------------------|----------------------|
| 1 pole          | G7L-1A-BUBJ | AC: 24, 100/120, 200/240 |                      |
| i pole          | G/L-1A-B0B0 | DC: 6, 12, 24, 48        | 20 pcs./tray         |
| 2 poles         | G7L-2A-BUBJ | AC: 24, 100/120, 200/240 | 20 pcs./iray         |
| z poies         | G/L-ZA-BUBJ | DC: 6, 12, 24, 48, 100   |                      |

When ordering, add uncompleted to the Exampleted Collaboration of the Exampleted Collaboration Note 1. When ordering, add the rated coil voltage to the model number.

However, the notation of the coil voltage on the product case as well as on the packing will be marked as  $\square\square$  VDC.

Note 2. Refer to the precautions on PCB Relays provided in General Information of the Relay Product Data Book, and "w -  $\square$  -3" for coil characteristics of AC operation.

# E-bracket/Adaptor/Socket/Cover

| Applicable Relay models   | Name                       | Model   | Minimum packing unit |
|---|----------------------------|---------|----------------------|
| G7L-1A-T<br>G7L-1A-TJ<br>G7L-1A-B<br>G7L-1A-BJ  | E-bracket                  | R99-07  | 10 pcs.              |
| G7L-2A-T<br>G7L-2A-TJ<br>G7L-2A-B<br>G7L-2A-BJ  | Adapter                    | P7LF-D  | 1 pcs.               |
| G7L-1A-T<br>G7L-1A-TJ<br>G7L-2A-T<br>G7L-2A-TJ  | Front-connecting<br>Socket | P7LF-06 | 1 pcs.               |
| G7L-1A-B<br>G7L-1A-BJ<br>G7L-1A-BUB<br>G7L-1A-BUBJ<br>G7L-2A-B<br>G7L-2A-BJ<br>G7L-2A-BJB<br>G7L-2A-BUB | Cover                      | P7LF-C  | 1 pcs.               |

Note. Order the models above in increments of the minimum quantity packaged.

# ■Ratings

## Coil

| Item           | Rated current | Coil resistance | Coil induc     | ctance (H)      | Must operate voltage | Must release voltage | Max.<br>permissible<br>voltage | Power consumption     |
|----------------|---------------|-----------------|----------------|-----------------|----------------------|----------------------|--------------------------------|-----------------------|
| Rated voltage  | (mA)          | (Ω)             | Armature<br>ON | Armature<br>OFF | On the b             | asis of rated        | voltage                        | (VA-Ŵ)                |
| 12 VAC         | 142           |                 |                |                 |                      |                      |                                |                       |
| 24 VAC         | 71            |                 |                |                 | 75% max.             | 15% min.             | 110%                           | Annua 17              |
| 50 VAC         | 34            |                 |                |                 |                      |                      |                                | Approx. 1.7<br>to 2.5 |
| 100 to 120 VAC | 17.0 to 20.4  |                 |                |                 | 75 V max.            | 18 V min.            | 132 V                          | 10 2.0                |
| 200 to 240 VAC | 8.5 to 10.2   | ľ               | ľ              | ľ               | 150 V max.           | 36 V min.            | 264 V                          |                       |
| 6 VDC          | 317           | 18.9            | 0.09           | 0.21            |                      |                      |                                |                       |
| 12 VDC         | 158           | 75              | 0.37           | 0.88            |                      |                      |                                |                       |
| 24 VDC         | 79            | 303             | 1.42           | 3.54            | 75% max.             | 15% min.             | 110%                           | Approx. 1.9           |
| 48 VDC         | 40            | 1220            | 6.1            | 15.3            | 1                    |                      |                                |                       |
| 100 VDC        | 19            | 5260            | 21.3           | 60.0            | 1                    |                      |                                |                       |

- Note 1. The rated current and coil resistance are measured at a coil temperature of 23°C with tolerances of +15%/-20% for AC rated current and ±15% for DC coil resistance.
  - 2. The inductances shown above are reference values.
  - 3. Performance characteristic data are measured at a coil temperature of 23°C.
  - 4. The maximum allowable coil voltage refers to the maximum value in a varying range of operating power voltage, measured at ambient temperature 23°C.

    5. The "to" (for example "100 to 120") represents the range of rated voltages.

## Contacts

| Contact Form           | G7L-1A-T□<br>G7L-1A-B□ |                                   | G7L-2A-T□<br>G7L-2A-B□ |                                   | G7L-1A-P<br>G7L-2A-P |                                   |
|------------------------|------------------------|-----------------------------------|------------------------|-----------------------------------|----------------------|-----------------------------------|
| load                   | Resistive<br>load      | Inductive load $(\cos\phi = 0.4)$ | Resistive load         | Inductive load (cos \$\phi = 0.4) | Resistive<br>load    | Inductive load (cos \$\phi = 0.4) |
| Contact type           | Double break           |                                   |                        |                                   |                      |                                   |
| Contact material       | Ag alloy               |                                   |                        |                                   |                      |                                   |
| Rated load             | 30 A at 220 VAC        |                                   |                        | 220 VAC                           |                      |                                   |
| Rated carry current    | 30 A 25 A 20 A         |                                   |                        | Α (                               |                      |                                   |
| Max. switching voltage | 250 VAC                |                                   |                        |                                   |                      |                                   |
| Max. switching current | 30 A 25 A 20 A         |                                   |                        | ) A                               |                      |                                   |

Note. When using B-series (screw) products, since the screw diameter of the contact terminal is M4, be careful that the contact current should be 20 A or less according to JET standard (electrical appliance and material control law of Japan).

# **■**Characteristics

| Contact resi                                   | stance *1  | 50 mΩ max.  |  |
|--|--|---|--|
| Operate time                                   |  | 30 ms max.  |  |
| Release tim                                    |  | 30 ms max.  |  |
| Max.   | Mechanical   | 1,800 operations/hr   |  |
| operating frequency                            | Rated load   | 1,800 operations/hr   |  |
| Insulation re                                  |  | 1,000 MΩ min  |  |
|  | Between coil and contacts                                    | 4,000 VAC min., 50/60 Hz<br>for 1 min   |  |
| Dielectric<br>strength                         | Between contacts of same polarity                            | 2 000 VAC 50/60 Hz for  |  |
| Sucrigur                                       | Between contacts<br>of different polarity<br>(DPST-NO model) | 2,000 VAC, 50/60 Hz for<br>1 min  |  |
| Impulse with                                   | nstand voltage   | 10,000 V between coil and contact *4  |  |
| Vibration                                      | Destruction  | 10 to 55 to 10 Hz, 0.75 mm<br>single amplitude<br>(1.5 mm double amplitude)   |  |
| resistance                                     | Malfunction  | 10 to 55 to 10 Hz, 0.75 mm<br>single amplitude<br>(1.5 mm double amplitude)   |  |
| Shock  | Destruction  | 1,000 m/s <sup>2</sup>  |  |
| resistance                                     | Malfunction  | 100 m/s <sup>2</sup>  |  |
|  | Mechanical   | 1,000,000 operations min.<br>(at 1,800 operations/hr)   |  |
| Endurance Electrical *5                        |  | 100,000 operations min.<br>(at 1,800 operations/hr<br>under rated load)   |  |
| Failure rate (P level)<br>(reference value *6) |  | 100 mA at 5 VDC   |  |
| Weight   |  | Approx. 90 g: Quick-connect terminal models Approx. 100 g: PCB terminal models Approx. 120 g: Screw terminal models |  |

- Note. \*1.
- The values given above are initial values.

  Measurement conditions: 5 VDC, 1 A, voltage drop
- Measurement conditions: Rated operating voltage applied, \*2. Measurement conditions: Rated operating voltage applied, not including contact bounce.

  Ambient temperature: 23°C
  Measurement conditions: The insulation resistance was measured with a 500-VDC megohmmeter at the same locations as the dielectric strength was measured.

  JEC-212 (1981) Standard Impulse Wave Type (1.2x50µs).


  Ambient temperature: 23°C
- \*3.


- Ambient temperature: 23°C
  This value was measured at a switching frequency of 60 operations/min.

| Ambient operating temperature | -25°C to 60°C<br>(with no icing or<br>condensation) |
|-------------------------------|---|
| Ambient operating humidity    | 5% to 85%   |
| Ambient operating humidity    | 5% to 85%   |


# **■**Engineering Data


# G7L-1A-T (TJ) (TUB) (TUBJ) G7L-1A-B (BJ) (BUB) (BUBJ) Maximum Switching Power







# G7L-2A-T (TJ) (TUB) (TUBJ) G7L-2A-B (BJ) (BUB) (BUBJ) Maximum Switching Power







## G7L-1A-P G7L-2A-P Maximum Switching Power






# Ambient Temperature vs. Operate and Release Voltage G7L-1A VAC (60 Hz)







# Ambient Temperature vs. Coil Temperature Rise G7L-1A 120 VAC (50 Hz)




#### G7L-1A VDC




# Shock Malfunction G7L-2A-T (TUB) 100 to 120 VAC




# Momentary Voltage Drop Test G7L-2A-T (TUB) 100 to 120 VAC Test Circuit



#### Wave resulted from test




# Voltage distribution of wave e which chattering does not occur.




# Characteristic variation resulted from different mounting directions G7L-2A-T (TUB) 100 to 120 VAC

#### Operate time


G 7 L




## Release time



## Operate voltage



## Release voltage




(Note.) The mounting direction A' deteriorates switching performance.


# Actual Load Endurance Test G7L-2A 100 to 200 VAC

# Operate and Release voltages

N = 5




#### Contact resistance




# Operate and Release voltages

N = 5




# Contact resistance



# Load conditions


# • 1 \$\phi\$ 220 VAC



Applied coil voltage: 100% of rated voltage

# Load conditions


# • 1 \$\phi\$ 220 VAC




Applied coil voltage: 100% of rated voltage

# G7L-2A 100 to 200 VAC

# Operate and Release voltages




## **Contact resistance**



# Operate and Release voltages

# N = 5 70 N = 5 Operate voltage 60 Operate voltage 40 Release volta 8 30 Release volta

## **Contact resistance**




## Load conditions

• 1 \$ 220 VAC



Applied coil voltage: 75% of rated voltage

# **Load conditions**



Applied coil voltage: 75% of rated voltage


# **■**Dimensions


# ● E-bracket Mounting Quick-connect Terminals

Note. E-brackets are sold separately.

## G7L-1A-T







#### Terminal Arrangement/ Internal Connections


(Top View)


(No coil polarity)

Note. Refer to page 12 for the coil internal connection diagram

## G7L-2A-T










(No coil polarity)
Note. Refer to page 12 for the coil internal connection diagram


## **Mounting Holes**



# G7L-1A-TJ (with Test Button)











(No coil polarity)
Note. Refer to page 12 for the coil internal connection diagram

G7L-2A-TJ (with Test Button)










(No coil polarity)
Note. Refer to page 12 for the coil internal connection diagram

# Adapter Mounting

Note 1. The DIN Track Mounting Adapter and DIN tracks are sold separately.

# **Quick-connect Terminals** $\hbox{2. The DIN Track Mounting Adapter can be track-mounted or screw-mounted}.$ G7L-1A-T **Terminal Arrangement/** Internal Connections P7LF-D PFP-□N (Top View) (No coil polarity) 63 max Note. Refer to page 12 for the coil internal connection diagram -66.5 max G7L-2A-T P7LF-D PFP-□N G7L 51.5 max **Mounting Holes** Two, M4 or 4.5-dia. holes (No coil polarity) 55.5 max 63 max Note. Refer to page 12 for the coil internal connection diagram -66.5 max G7L-1A-TJ P7LF-D PFP-□N (with Test Button) G7I



Test button

-63 max


-66.5 max.

# • Front-connecting Socket Mounting **Quick-connect Terminals**

Note 1. The Front-connecting Socket and DIN tracks are sold separately. 2. The Front-connecting Socket can be track-mounted or screw-mounted.

(No coil polarity)

Note. Refer to page 12 for the coil internal connection diagram







PFP-□N 2-M3.5 × 6 (coil side)

P7LF-06

G7L

F51.5 max.

Test button
61.5 max.

5 No.

Terminal Arrangement/ Internal Connections (Top View)



(No coil polarity)


Note. Refer to page 12 for the coil internal connection diagram

Mounting Holes



G7L-2A-TJ (with Test Button)









(No coil polarity)
Note. Refer to page 12 for the coil internal
connection diagram

## Upper Bracket Mounting Quick-connect Terminals











# Terminal Arrangement/ Internal Connections





(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram

G7L-2A-TUB











(No coil polarity)
Note. Refer to page 12 for the coil internal connection diagram


Mounting Holes




# G7L-1A-TUBJ (with Test Button)












(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram

G7L-2A-TUBJ (with Test Button)










(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram

Note. E-brackets are sold separately.

# G7L-1A-B



2-M3.5 × 6 (coil side) 52.5 max. 50.5 max.



Terminal Arrangement/
Internal Connections


(Top View)




(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram

G7L-2A-B










(No coil polarity)
Note. Refer to page 12 for the coil internal connection diagram


Mounting Holes



G7L-1A-BJ (with Test Button)











(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram

G7L-2A-BJ (with Test Button)









(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram


## Adapter Mounting Screw Terminals


Note 1. The DIN Track Mounting Adapter and DIN tracks are sold separately.

2. The DIN Track Mounting Adapter can be track-mounted or screw-mounted.

# G7L-1A-B







## Terminal Arrangement/ Internal Connections

(Top View)




(No coil polarity)
Note. Refer to page 12 for the coil
internal connection diagram

**Mounting Holes** 




# G7L-2A-B








(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram





#### Terminal Arrangement/ Internal Connections



(No coil polarity)


Note. Refer to page 12 for the coil internal connection diagram

Two, M4 or 4.5-dia.

40±0.1

G7L-2A-BJ (with Test Button)









(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram

# Upper Bracket Mounting Screw Terminals


## G7L-1A-BUB








Terminal Arrangement/ Internal Connections (Top View)





(No coil polarity)
Note. Refer to page 12 for the coil internal connection diagram

G7L-2A-BUB











(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram


**Mounting Holes** 




# G7L-1A-BUBJ (with Test Button)












(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram

# G7L-2A-BUBJ (with Test Button)










(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram

# G7L-1A-P




2.8 52.5 max.



Terminal Arrangement/
Internal Connections
(Bottom View)





(No coil polarity)
Note. Refer to page 12 for the coil internal
connection diagram



G7L-2A-P








Two, 4.5-dia. hole

Terminal Arrangement/ Internal Connections




(No coil polarity) Note. Refer to page 12 for the coil internal connection diagram


PCB Mounting Holes (Bottom View) Tolerance: ±0.1 mm



# ● E-bracket R99-07 (E KANAGU) FOR G7L










**Mounting Holes** 



# ■ Adapter P7LF-D









# **Mounting Holes**



# Front-connecting SocketP7LF-06









# Mounting Holes



# ● Cover P7LF-C







Put the P7LF-C cover onto the terminals in order to protect the user from electric shock.

# **Approved Standards**

 $\cdot$  A variety of Safety Standard approved products for standard models.

# UL Recognized (File No. E41643)

| Model                 | Coil ratings                  | Contact ratings              | Number of test operations |
|-----------------------|-------------------------------|------------------------------|---------------------------|
|                       |                               | 30 A, 277 VAC (RES) 40°C     | 100,000                   |
| G7L-1A-T□             |                               | 1.5 kW, 120 VAC (T) 40°C     | 6,000                     |
| G7L-1A-B□<br>G7L-1A-P | 12 to 240 VAC<br>6 to 220 VDC | 1.5 HP, 120 VAC 40°C         | 1,000                     |
| G7L-1A-F<br>G7L-2A-T□ |                               | 3 HP 277 VAC 40°C            | 100,000                   |
| G7L-2A-1□             |                               | 20 FLA/120 LRA, 120 VAC 40°C | 30.000                    |
| G7L-2A-P              |                               | 17 FLA/102 LRA, 277 VAC 40°C | 30,000                    |
|                       |                               | TV-10, 120 VAC 40°C          | 25,000                    |

# CSA certified (File No. LR31928)

| Model     | Coil ratings  | Contact ratings                | Number of test |
|-----------|---------------|--------------------------------|----------------|
|           | our ramingo   | Comac rainigo                  | operations     |
|           |               | 2.4 kW, 120 VAC (T) 40°C       | 6,000          |
|           | 12 to 240 VAC | 1.5 HP, 120 VAC (T) 40°C       | 1,000          |
| G7L-1A-P  | 6 to 220 VDC  | 3 HP 277 VAC 40°C              | 1,000          |
|           | 010220 100    | 20.5 FLA/105 LRA, 120 VAC 85°C | 100,000        |
|           |               | TV-10, 120 VAC 40°C            | 25,000         |
| G7L-1A-T□ |               | 30 A, 277 VAC (RES) 40°C       | 100,000        |
| G7L-1A-B□ |               | 2.4 kW, 120 VAC (T) 40°C       | 6,000          |
|           | 12 to 240 VAC | 1.5 HP, 120 VAC 40°C           | 1.000          |
| G7L-2A-T□ | 6 to 220 VDC  | 3 HP 277 VAC 40°C              | 1,000          |
| G7L-2A-B□ |               | 20.5 FLA/105 LRA, 120 VAC 85°C | 100,000        |
| G7L-2A-P  |               | TV-10, 120 VAC 40°C            | 25,000         |

#### ● Reference

UL Approved Type .....

UL508 Industrial Control Devices

UL1950 Information processing equipment

(Including office equipment)

CSA Approved Type .....

CSA C22.2 No.1, 14

**Industrial Control Devices** 

CSA C22.2 No.950 Information processing equipment

(Including office equipment)

TÜV EN/IEC Standard Approved Type.....

EN61810-1 Relay

# EN/IEC, TÜV Certified (Certificate No. R50059083)

| Model     | Coil ratings              | Contact ratings  | Approved switching operations |
|-----------|---------------------------|--|-------------------------------|
|           |                           | SPST-NO (1a)   |                               |
| G7L-1A-B□ |                           | 30 A, 250 VAC ~ (cosφ = 1) 60°C  | 50,000                        |
| G/L IX D  |                           | 25 A, 250 VAC ~ (cosφ = 0.4) 60°C  | 30,000                        |
|           |                           | 30 A, 120 VAC ~ $(\cos \phi = 0.4) 60^{\circ}$ C                         |                               |
|           |                           | DPST-NO (2a)   |                               |
| G7L-2A-B□ |                           | 25 A, 277 VAC ~ (cosφ = 1) 60°C  | 50,000                        |
|           |                           | 25 A, 277 VAC ~ (cosφ = 0.4) 60°C  |                               |
|           |                           | SPST-NO (1a)   |                               |
|           |                           | 25 A, 240 VAC ~ (cosφ = 1) 60°C  |                               |
| G7L-1A-T□ |                           | 25 A, 240 VAC ~ (cosφ = 0.4) 60°C  | 50,000                        |
|           | 6, 12, 24, 48,            | 25 A, 277 VAC ~ (cosφ = 1) 60°C  |                               |
|           | 100, 110, 200,            | 25 A, 277 VAC ~ (cosφ = 0.4) 60°C  |                               |
|           | 220 VDC                   | DPST-NO (2a)   |                               |
|           | 12, 24, 50,               | 25 A, 240 VAC ~ (cosφ = 1) 60°C  |                               |
| G7L-2A-T□ | 100 to 120,<br>200 to 240 | $25 \text{ A}, 240 \text{ VAC} \sim (\cos\phi = 0.4) 60^{\circ}\text{C}$ | 50,000                        |
|           | 200 to 240<br>VAC         | $25 \text{ A}, 277 \text{ VAC} \sim (\cos \phi = 1) 60^{\circ}\text{C}$  |                               |
|           | VAC                       | 25 A, 277 VAC ~ (cosφ = 0.4) 60°C  |                               |
|           |                           | SPST-NO (1a)   |                               |
| 071 44 0  |                           | 20 A, 240 VAC ~ (cosφ = 1) 60°C  | F0 000                        |
| G7L-1A-P  |                           | 20 A, 240 VAC ~ (cosφ = 0.4) 60°C  | 50,000                        |
|           |                           | 25 A, 277 VAC ~ (cosφ = 1) 60°C  |                               |
|           | -                         | 25 A, 277 VAC ~ (cosφ = 0.4) 60°C  |                               |
|           |                           | DPST-NO (2a)   |                               |
| G7L-2A-P  |                           | 20 A, 240 VAC ~ (cosφ = 1) 60°C  | E0 000                        |
| G/L-2A-P  |                           | 20 A, 240 VAC ~ (cosφ = 0.4) 60°C  | 50,000                        |
|           |                           | 25 A, 277 VAC ~ (cosφ = 1) 60°C<br>25 A, 277 VAC ~ (cosφ = 0.4) 60°C     |                               |
|           |                           | 23 A, 277 VAC ~ (COSψ = 0.4) 60 C  |                               |

# ■Precautions

## Please refer to "PCB Relays Common Precautions" for general precautions.

## **Correct Use**

#### Installation

- Although there are not specific limits on the installation site, it should be as dry and dust-free as possible.
- Using in an atmosphere of high temperature, high humidity and corrosive gas may deteriorate its performance characteristic caused by condensation or corrosive products, resulting in failure or burn damage of the Relay.
- PCB Terminal-equipped Relays weigh approximately 100 g.
   Be sure that the PCB is strong enough to support them. We recommend dual-side through-hole PCBs to reduce solder cracking from heat stress.
- Relays with test buttons must be mounted facing down.
   Be careful not to touch the test button accidentally. Doing so may turn ON
- Be sure to use the test button for test purposes only (with test-button models). The test button is used for Relay circuit tests, such as circuit continuity tests. Do not attempt to switch the load with the test button.

#### Micro Loads

the contact.

 The G7L is used for switching power loads, such as motor, transformer, solenoid, lamp, and heater loads. Do not use the G7L for switching micro loads, such as signals.

## Soldering PCB Terminals

- Do not perform automatic soldering but solder manually.
- Solder with the following conditions: Soldering iron temperature (max.) 380°C, Soldering time within 10 seconds.
- Do not wash down the entire Relay because it does not have an airtight construction.

#### Connecting

 Refer to the following table when connecting a wire with a crimpstyle terminal to the G7L.

|         | Screw terminals      | Front-connecting<br>Socket |
|---------|----------------------|----------------------------|
| Coil    | 5.8<br>5<br>M3.5     | 6.5<br>5.3<br>M3.5         |
| Contact | M4<br>5.5<br>6.5<br> | M4<br>5.5<br>7<br>7        |

 Allow suitable slack on leads when wiring, and do not apply excessive force to the terminals.

· Tightening torque

 When connecting with screws, if the screws are not sufficiently tightened, the lead wire can become detached and may lead to abnormal heating or fire caused by faulty contact.

Mounting Torque
0.98N · m
Tighten with two M4 screws when mounting.
(Top bracket type)

- Do not apply excessive force when mounting or dismounting the Faston receptacle. Insert and remove terminals carefully one at a time. Do not insert terminals at an angle, or insert/remove multiple terminals at the same time.
- Do not connect to the terminals by soldering
- Refer to the following table for recommendations of connectors made by OMRON.

| Туре                               | Receptacle terminals                         | Housing       |
|------------------------------------|--|---------------|
| #250 terminals<br>(width: 6.35 mm) | XT3W-S441-12<br>XT3W-S442-12<br>XT3W-S443-12 | XT3B-1S white |

Note. The current should be 25 A when using receptacle terminals.


#### Reference Data


 The ratio of rated voltage between 100 to 120 VAC are values measured on the basis of 100 VAC.

# Operating Coil

(Coil internal connections diagram)

DC Coil





- If a transistor drives the G7L check the leakage current, and connect a bleeder resistor if necessary.
- The AC coil is provided with a built-in full-wave rectifier. If a triac, such as an SSR, drives the G7L, the G7L may not release. Be sure to perform a trial operation with the G7L and the triac before applying them to actual use.

# DIN Track Mounting Adapter and Front-connecting Socket

(DIN Track Mounting)

- The DIN Track Mounting Adapter and Front-connecting Socket can be mounted on the G7L with just one hand and dismounted with ease by using a screwdriver.
- To support the G7L mounted on a DIN Track Mounting Adapter or Front-connecting Socket, use the PFP-M End Plate. Put the End Plate onto the DIN Track Mounting Adapter or Front-connecting Socket so that the surface mark of the End Plate faces upwards. Then tighten the screw of the End Plate securely with a screwdriver.

# (Screw Mounting)

- Screw-mount the DIN Track Mounting Adapter or Front-connecting Socket securely after opening screw mounting holes on them.
- When cutting or opening holes on the panel after the Front-connecting Socket is mounted, take proper measures so that the cutting chips will not fall onto the Relay terminals. When cutting or opening holes on the upper part of the panel, mask the Front-connecting Socket properly with a cover.

Application examples provided in this document are for reference only. In actual applications, confirm equipment functions and safety before using the product.
 Consult your OMRON representative before using the product under conditions which are not described in the manual or applying the product to nuclear control systems, railroad systems, aviation systems, vehicles, combustion systems, medical equipment, amusement machines, safety equipment, and other systems or equipment that may have a serious influence on lives and property if used improperly. Make sure that the ratings and performance characteristics of the product provide a margin of safety for the system or equipment, and be sure to provide the system or equipment with double safety mechanisms.

Note: Do not use this document to operate the Unit.

Contact: www.omron.com/ecb

**OMRON Corporation** 

**Electronic and Mechanical Components Company** 

Cat. No. J055-E1-15 0519(0207)(O)