


Miniature Basic Switch

D3V

Reliable Basic Switch with External Lever

- Available by 0.1 A, 6 A, 11 A, 16 A and 21 A models, all with self-cleaning contacts.
- Available with internally or externally fitted levers, and 2 fixing positions for external levers.
- Conforms to EN61058-1 and UL1054.



Ordering Information

■ Model Number Legend

D3V-□□□□-□□□□-□□□
1 2 3 4 5 6 7 8 9

1. Ratings

21:	20 (4) A at 250 VAC
16:	16 (3) A at 250 VAC
11:	11 (3) A at 250 VAC
6:	6 (2) A at 250 VAC
01:	0.1 A at 125 VAC

2. Contact Gap

None:	1 mm (F gap)
G:	0.5 mm (G gap)

3. Actuator

None:	Pin plunger
1:	Short hinge lever
2:	Hinge lever
3:	Long hinge lever
4:	Simulated roller lever
5:	Short hinge roller lever
6:	Hinge roller lever

4. Hinge Position

None:	Internal/Far from plunger
M:	External/Far from plunger
K:	External/Near plunger

5. Contact Form

1:	SPDT
2:	SPST-NC
3:	SPST-NO

6. Terminals

A:	Solder terminals
C2:	Quick-connect terminals (#187)
C:	Quick-connect terminals (#250)

7. Maximum Operating Force

5:	1.96 N {200 gf}
4A:	1.23 N {125 gf}
4:	0.98 N {100 gf}
3:	0.49 N {50 gf}
2:	0.25 N {25 gf}

Note: These values are for the pin plunger models.

8. Mounting Hole Size

None:	3.1 mm
K:	2.9 mm

9. Special Code

None:	Standard
H:	High temperature (125°C)
E:	Special rating: 21 (8) A

■ Available Combinations

Heat resis- tance	Model	D3V-21		D3V-16			D3V-11					D3V-6				D3V-01	
		21 A		16 A			11 A					6 A				0.1 A	
		1.23 N {125 gf}		1.96 N {200 gf}		0.98 N {100 gf}	1.96 N {200 gf}		0.98 N {100 gf}		0.49 N {50 gf}	1.96 N {200 gf}		0.98 N {100 gf}		0.49 N {50 gf}	0.25 N {25 gf}
		G		F	G	F/G	F	G	F	G	G	F/G		F	G	G	F
Standard (85°C)	#187																●
	#250	●															○
Standard (105°C)	#187		●	○	○		●	○	●	○	○	○	●	○	●		
	#250		●	○	○		●	○	●	○	○	○	●	○	●		
High tem- perature (125°C)	#187		○	○	○		○	○	○	○	○	○	○	○	○		
	#250		○	○	○		○	○	○	○	○	○	○	○	○		

Note: 1. ●: Standard
○: Semi-standard

2. Consult your OMRON sales representative for specific models with standard approvals.

■ List of Models

- 21 A (OF: 1.23 N {125 gf})

Actuator	Hinge position	Contact form		
		SPDT	SPST-NC	SPST-NO
Pin plunger 	---	D3V-21G-1□4A-Δ	D3V-21G-2□4A-Δ	D3V-21G-3□4A-Δ
Short hinge lever 	Internal	D3V-21G1-1□4A-Δ	D3V-21G1-2□4A-Δ	D3V-21G1-3□4A-Δ
	M	D3V-21G1M-1□4A-Δ	D3V-21G1M-2□4A-Δ	D3V-21G1M-3□4A-Δ
Hinge lever 	Internal	D3V-21G2-1□4A-Δ	D3V-21G2-2□4A-Δ	D3V-21G2-3□4A-Δ
	M	D3V-21G2M-1□4A-Δ	D3V-21G2M-2□4A-Δ	D3V-21G2M-3□4A-Δ
Long hinge lever 	Internal	D3V-21G3-1□4A-Δ	D3V-21G3-2□4A-Δ	D3V-21G3-3□4A-Δ
	M	D3V-21G3M-1□4A-Δ	D3V-21G3M-2□4A-Δ	D3V-21G3M-3□4A-Δ
Simulated roller lever 	Internal	D3V-21G4-1□4A-Δ	D3V-21G4-2□4A-Δ	D3V-21G4-3□4A-Δ
	M	D3V-21G4M-1□4A-Δ	D3V-21G4M-2□4A-Δ	D3V-21G4M-3□4A-Δ
Short hinge roller lever 	Internal	D3V-21G5-1□4A-Δ	D3V-21G5-2□4A-Δ	D3V-21G5-3□4A-Δ
	M	D3V-21G5M-1□4A-Δ	D3V-21G5M-2□4A-Δ	D3V-21G5M-3□4A-Δ
Hinge roller lever 	Internal	D3V-21G6-1□4A-Δ	D3V-21G6-2□4A-Δ	D3V-21G6-3□4A-Δ
	M	D3V-21G6M-1□4A-Δ	D3V-21G6M-2□4A-Δ	D3V-21G6M-3□4A-Δ

- 16 A (OF: 1.96 N {200 gf})

Actuator	Hinge position	Contact form		
		SPDT	SPST-NC	SPST-NO
Pin plunger 	---	D3V-16-1□5-Δ	D3V-16-2□5-Δ	D3V-16-3□5-Δ
Short hinge lever 	Internal	D3V-161-1□5-Δ	D3V-161-2□5-Δ	D3V-161-3□5-Δ
	M	D3V-161M-1□5-Δ	D3V-161M-2□5-Δ	D3V-161M-3□5-Δ
Hinge lever 	Internal	D3V-162-1□5-Δ	D3V-162-2□5-Δ	D3V-162-3□5-Δ
	M	D3V-162M-1□5-Δ	D3V-162M-2□5-Δ	D3V-162M-3□5-Δ
Long hinge lever 	Internal	D3V-163-1□5-Δ	D3V-163-2□5-Δ	D3V-163-3□5-Δ
	M	D3V-163M-1□5-Δ	D3V-163M-2□5-Δ	D3V-163M-3□5-Δ
Simulated roller lever 	Internal	D3V-164-1□5-Δ	D3V-164-2□5-Δ	D3V-164-3□5-Δ
	M	D3V-164M-1□5-Δ	D3V-164M-2□5-Δ	D3V-164M-3□5-Δ
Short hinge roller lever 	Internal	D3V-165-1□5-Δ	D3V-165-2□5-Δ	D3V-165-3□5-Δ
	M	D3V-165M-1□5-Δ	D3V-165M-2□5-Δ	D3V-165M-3□5-Δ
Hinge roller lever 	Internal	D3V-166-1□5-Δ	D3V-166-2□5-Δ	D3V-166-3□5-Δ
	M	D3V-166M-1□5-Δ	D3V-166M-2□5-Δ	D3V-166M-3□5-Δ

Note: The □ in the model number is for the terminal code.

A: Solder terminals

C2: Quick-connect terminals (#187)

C: Quick-connect terminals (#250)

The Δ in the model number is for the mounting hole size.


None: 3.1 mm

K: 2.9 mm

- 16 A (OF: 0.98 N {100 gf})

Actuator	Hinge position	Contact form		
		SPDT	SPST-NC	SPST-NO
Pin plunger 	---	D3V-16-1□4-Δ	D3V-16-2□4-Δ	D3V-16-3□4-Δ
Short hinge lever 	Internal	D3V-161-1□4-Δ	D3V-161-2□4-Δ	D3V-161-3□4-Δ
	M	D3V-161M-1□4-Δ	D3V-161M-2□4-Δ	D3V-161M-3□4-Δ
Hinge lever 	Internal	D3V-162-1□4-Δ	D3V-162-2□4-Δ	D3V-162-3□4-Δ
	M	D3V-162M-1□4-Δ	D3V-162M-2□4-Δ	D3V-162M-3□4-Δ
Long hinge lever 	Internal	D3V-163-1□4-Δ	D3V-163-2□4-Δ	D3V-163-3□4-Δ
	M	D3V-163M-1□4-Δ	D3V-163M-2□4-Δ	D3V-163M-3□4-Δ
Simulated roller lever 	Internal	D3V-164-1□4-Δ	D3V-164-2□4-Δ	D3V-164-3□4-Δ
	M	D3V-164M-1□4-Δ	D3V-164M-2□4-Δ	D3V-164M-3□4-Δ
Short hinge roller lever 	Internal	D3V-165-1□4-Δ	D3V-165-2□4-Δ	D3V-165-3□4-Δ
	M	D3V-165M-1□4-Δ	D3V-165M-2□4-Δ	D3V-165M-3□4-Δ
Hinge roller lever 	Internal	D3V-166-1□4-Δ	D3V-166-2□4-Δ	D3V-166-3□4-Δ
	M	D3V-166M-1□4-Δ	D3V-166M-2□4-Δ	D3V-166M-3□4-Δ

- 11 A (OF: 1.96 N {200 gf})

Actuator	Hinge position	Contact form		
		SPDT	SPST-NC	SPST-NO
Pin plunger 	---	D3V-11-1□5-Δ	D3V-11-2□5-Δ	D3V-11-3□5-Δ
Short hinge lever 	Internal	D3V-111-1□5-Δ	D3V-111-2□5-Δ	D3V-111-3□5-Δ
	M	D3V-111M-1□5-Δ	D3V-111M-2□5-Δ	D3V-111M-3□5-Δ
Hinge lever 	Internal	D3V-112-1□5-Δ	D3V-112-2□5-Δ	D3V-112-3□5-Δ
	M	D3V-112M-1□5-Δ	D3V-112M-2□5-Δ	D3V-112M-3□5-Δ
Long hinge lever 	Internal	D3V-113-1□5-Δ	D3V-113-2□5-Δ	D3V-113-3□5-Δ
	M	D3V-113M-1□5-Δ	D3V-113M-2□5-Δ	D3V-113M-3□5-Δ
Simulated roller lever 	Internal	D3V-114-1□5-Δ	D3V-114-2□5-Δ	D3V-114-3□5-Δ
	M	D3V-114M-1□5-Δ	D3V-114M-2□5-Δ	D3V-114M-3□5-Δ
Short hinge roller lever 	Internal	D3V-115-1□5-Δ	D3V-115-2□5-Δ	D3V-115-3□5-Δ
	M	D3V-115M-1□5-Δ	D3V-115M-2□5-Δ	D3V-115M-3□5-Δ
Hinge roller lever 	Internal	D3V-116-1□5-Δ	D3V-116-2□5-Δ	D3V-116-3□5-Δ
	M	D3V-116M-1□5-Δ	D3V-116M-2□5-Δ	D3V-116M-3□5-Δ

Note: The □ in the model number is for the terminal code.

A: Solder terminals

C2: Quick-connect terminals (#187)

C: Quick-connect terminals (#250)

The Δ in the model number is for the mounting hole size.

None: 3.1 mm

K: 2.9 mm

- 11 A (OF: 0.98 N {100 gf})

Actuator	Hinge position	Contact form		
		SPDT	SPST-NC	SPST-NO
Pin plunger 	---	D3V-11-1□4-Δ	D3V-11-2□4-Δ	D3V-11-3□4-Δ
Short hinge lever 	Internal	D3V-111-1□4-Δ	D3V-111-2□4-Δ	D3V-111-3□4-Δ
	M	D3V-111M-1□4-Δ	D3V-111M-2□4-Δ	D3V-111M-3□4-Δ
Hinge lever 	Internal	D3V-112-1□4-Δ	D3V-112-2□4-Δ	D3V-112-3□4-Δ
	M	D3V-112M-1□4-Δ	D3V-112M-2□4-Δ	D3V-112M-3□4-Δ
Long hinge lever 	Internal	D3V-113-1□4-Δ	D3V-113-2□4-Δ	D3V-113-3□4-Δ
	M	D3V-113M-1□4-Δ	D3V-113M-2□4-Δ	D3V-113M-3□4-Δ
Simulated roller lever 	Internal	D3V-114-1□4-Δ	D3V-114-2□4-Δ	D3V-114-3□4-Δ
	M	D3V-114M-1□4-Δ	D3V-114M-2□4-Δ	D3V-114M-3□4-Δ
Short hinge roller lever 	Internal	D3V-115-1□4-Δ	D3V-115-2□4-Δ	D3V-115-3□4-Δ
	M	D3V-115M-1□4-Δ	D3V-115M-2□4-Δ	D3V-115M-3□4-Δ
Hinge roller lever 	Internal	D3V-116-1□4-Δ	D3V-116-2□4-Δ	D3V-116-3□4-Δ
	M	D3V-116M-1□4-Δ	D3V-116M-2□4-Δ	D3V-116M-3□4-Δ

- 11 A (OF: 0.49 N {50 gf})

Actuator	Hinge position	Contact form		
		SPDT	SPST-NC	SPST-NO
Pin plunger 	---	D3V-11G-1□3-Δ	D3V-11G-2□4-Δ	D3V-11G-3□3-Δ
Short hinge lever 	Internal	D3V-11G1-1□3-Δ	D3V-11G1-2□4-Δ	D3V-11G1-3□3-Δ
	M	D3V-11G1M-1□3-Δ	D3V-11G1M-2□4-Δ	D3V-11G1M-3□3-Δ
Hinge lever 	Internal	D3V-11G2-1□3-Δ	D3V-11G2-2□3-Δ	D3V-11G2-3□3-Δ
	M	D3V-11G2M-1□3-Δ	D3V-11G2M-2□3-Δ	D3V-11G2M-3□3-Δ
Long hinge lever 	Internal	D3V-11G3-1□3-Δ	D3V-11G3-2□3-Δ	D3V-11G3-3□3-Δ
	M	D3V-11G3M-1□3-Δ	D3V-11G3M-2□3-Δ	D3V-11G3M-3□3-Δ
Simulated roller lever 	Internal	D3V-11G4-1□3-Δ	D3V-11G4-2□3-Δ	D3V-11G4-3□3-Δ
	M	D3V-11G4M-1□3-Δ	D3V-11G4M-2□3-Δ	D3V-11G4M-3□3-Δ
Short hinge roller lever 	Internal	D3V-11G5-1□3-Δ	D3V-11G5-2□3-Δ	D3V-11G5-3□3-Δ
	M	D3V-11G5M-1□3-Δ	D3V-11G5M-2□3-Δ	D3V-11G5M-3□3-Δ
Hinge roller lever 	Internal	D3V-11G6-1□3-Δ	D3V-11G6-2□3-Δ	D3V-11G6-3□3-Δ
	M	D3V-11G6M-1□3-Δ	D3V-11G6M-2□3-Δ	D3V-11G6M-3□3-Δ

Note: The □ in the model number is for the terminal code.

A: Solder terminals

C2: Quick-connect terminals (#187)

C: Quick-connect terminals (#250)

The Δ in the model number is for the mounting hole size.

None: 3.1 mm

K: 2.9 mm

- 6 A (OF: 0.98 N {100 gf})

Actuator	Hinge position	Contact form		
		SPDT	SPST-NC	SPST-NO
Pin plunger 	---	D3V-6-1□4-Δ	D3V-6-2□4-Δ	D3V-6-3□4-Δ
Short hinge lever 	Internal	D3V-61-1□4-Δ	D3V-61-2□4-Δ	D3V-61-3□4-Δ
	M	D3V-61M-1□4-Δ	D3V-61M-2□4-Δ	D3V-61M-3□4-Δ
Hinge lever 	Internal	D3V-62-1□4-Δ	D3V-62-2□4-Δ	D3V-62-3□4-Δ
	M	D3V-62M-1□4-Δ	D3V-62M-2□4-Δ	D3V-62M-3□4-Δ
Long hinge lever 	Internal	D3V-63-1□4-Δ	D3V-63-2□4-Δ	D3V-63-3□4-Δ
	M	D3V-63M-1□4-Δ	D3V-63M-2□4-Δ	D3V-63M-3□4-Δ
Simulated roller lever 	Internal	D3V-64-1□4-Δ	D3V-64-2□4-Δ	D3V-64-3□4-Δ
	M	D3V-64M-1□4-Δ	D3V-64M-2□4-Δ	D3V-64M-3□4-Δ
Short hinge roller lever 	Internal	D3V-65-1□4-Δ	D3V-65-2□4-Δ	D3V-65-3□4-Δ
	M	D3V-65M-1□4-Δ	D3V-65M-2□4-Δ	D3V-65M-3□4-Δ
Hinge roller lever 	Internal	D3V-66-1□4-Δ	D3V-66-2□4-Δ	D3V-66-3□4-Δ
	M	D3V-66M-1□4-Δ	D3V-66M-2□4-Δ	D3V-66M-3□4-Δ

- 6 A (OF: 0.49 N {50 gf})

Actuator	Hinge position	Contact form		
		SPDT	SPST-NC	SPST-NO
Pin plunger 	---	D3V-6G-1□3-Δ	D3V-6G-2□3-Δ	D3V-6G-3□3-Δ
Short hinge lever 	Internal	D3V-6G1-1□3-Δ	D3V-6G1-2□3-Δ	D3V-6G1-3□3-Δ
	M	D3V-6G1M-1□3-Δ	D3V-6G1M-2□3-Δ	D3V-6G1M-3□3-Δ
Hinge lever 	Internal	D3V-6G2-1□3-Δ	D3V-6G2-2□3-Δ	D3V-6G2-3□3-Δ
	M	D3V-6G2M-1□3-Δ	D3V-6G2M-2□3-Δ	D3V-6G2M-3□3-Δ
Long hinge lever 	Internal	D3V-6G3-1□3-Δ	D3V-6G3-2□3-Δ	D3V-6G3-3□3-Δ
	M	D3V-6G3M-1□3-Δ	D3V-6G3M-2□3-Δ	D3V-6G3M-3□3-Δ
Simulated roller lever 	Internal	D3V-6G4-1□3-Δ	D3V-6G4-2□3-Δ	D3V-6G4-3□3-Δ
	M	D3V-6G4M-1□3-Δ	D3V-6G4M-2□3-Δ	D3V-6G4M-3□3-Δ
Short hinge roller lever 	Internal	D3V-6G5-1□3-Δ	D3V-6G5-2□3-Δ	D3V-6G5-3□3-Δ
	M	D3V-6G5M-1□3-Δ	D3V-6G5M-2□3-Δ	D3V-6G5M-3□3-Δ
Hinge roller lever 	Internal	D3V-6G6-1□3-Δ	D3V-6G6-2□3-Δ	D3V-6G6-3□3-Δ
	M	D3V-6G6M-1□3-Δ	D3V-6G6M-2□3-Δ	D3V-6G6M-3□3-Δ

Note: The □ in the model number is for the terminal code.

A: Solder terminals

C2: Quick-connect terminals (#187)


C: Quick-connect terminals (#250)

The Δ in the model number is for the mounting hole size.

None: 3.1 mm

K: 2.9 mm

- 01 A (OF: 0.49 N {50 gf})

Actuator	Hinge position	Contact form		
		SPDT	SPST-NC	SPST-NO
Pin plunger 	---	D3V-01-1□3-Δ	D3V-01-2□3-Δ	D3V-01-3□3-Δ
Short hinge lever 	Internal	D3V-011-1□3-Δ	D3V-011-2□3-Δ	D3V-011-3□3-Δ
	M	D3V-011M-1□3-Δ	D3V-011M-2□3-Δ	D3V-011M-3□3-Δ
Hinge lever 	Internal	D3V-012-1□3-Δ	D3V-012-2□3-Δ	D3V-012-3□3-Δ
	M	D3V-012M-1□3-Δ	D3V-012M-2□3-Δ	D3V-012M-3□3-Δ
Long hinge lever 	Internal	D3V-013-1□3-Δ	D3V-013-2□3-Δ	D3V-013-3□3-Δ
	M	D3V-013M-1□3-Δ	D3V-013M-2□3-Δ	D3V-013M-3□3-Δ
Simulated roller lever 	Internal	D3V-014-1□3-Δ	D3V-014-2□3-Δ	D3V-014-3□3-Δ
	M	D3V-014M-1□3-Δ	D3V-014M-2□3-Δ	D3V-014M-3□3-Δ
Short hinge roller lever 	Internal	D3V-015-1□3-Δ	D3V-015-2□3-Δ	D3V-015-3□3-Δ
	M	D3V-015M-1□3-Δ	D3V-015M-2□3-Δ	D3V-015M-3□3-Δ
Hinge roller lever 	Internal	D3V-016-1□3-Δ	D3V-016-2□3-Δ	D3V-016-3□3-Δ
	M	D3V-016M-1□3-Δ	D3V-016M-2□3-Δ	D3V-016M-3□3-Δ

- 01 A (OF: 0.25 N {25 gf})

Actuator	Hinge position	Contact form		
		SPDT	SPST-NC	SPST-NO
Pin plunger 	---	D3V-01-1□2-Δ	D3V-01-2□2-Δ	D3V-01-3□2-Δ

Note: The □ in the model number is for the terminal code.
 A: Solder terminals
 C2: Quick-connect terminals (#187)
 C: Quick-connect terminals (#250)
 The Δ in the model number is for the mounting hole size.
 None: 3.1 mm
 K: 2.9 mm

Specifications

■ Ratings

Type	Rated voltage	Non-inductive load				Inductive load			
		Resistive load		Lamp load		Inductive load		Motor load	
		NC	NO	NC	NO	NC	NO	NC	NO
D3V-21	250 VAC	21 A		3 A		12 A		4 A	
	8 VDC	21 A		5 A		12 A		7 A	
	30 VDC	14 A		5 A		12 A		5 A	
	125 VDC	0.6 A		0.1 A		0.6 A		0.1 A	
	250 VDC	0.3 A		0.05 A		0.3 A		0.05 A	
D3V-16	250 VAC	16 A		2 A		10 A		3 A	
	8 VDC	16 A		4 A		10 A		6 A	
	30 VDC	10 A		4 A		10 A		4 A	
	125 VDC	0.6 A		0.1 A		0.6 A		0.1 A	
	250 VDC	0.3 A		0.05 A		0.3 A		0.05 A	
D3V-11	250 VAC	11 A		1.5 A		6 A		2 A	
	8 VDC	11 A		3 A		6 A		3 A	
	30 VDC	6 A		3 A		6 A		3 A	
	125 VDC	0.6 A		0.1 A		0.6 A		0.1 A	
	250 VDC	0.3 A		0.05 A		0.3 A		0.05 A	
D3V-6	250 VAC	6 A		3 A		4 A		---	
	8 VDC	6 A		3 A		4 A		---	
	30 VDC	6 A		3 A		4 A			
	125 VDC	0.4 A		0.1 A		0.4 A			
	250 VDC	0.3 A		0.05 A		0.2 A			
D3V-01	125 VAC	0.1 A		---		---		---	
	8 VDC	0.1 A		---		---		---	
	30 VDC	0.1 A							

- Note:**
1. The above current values are the normal current values of models with a contact gap of 1 mm (gap F), which vary with the normal current values of models with a contact gap of 0.5 mm (gap G).
 2. Inductive load has a power factor of 0.4 min. (AC) and a time constant of 7 ms max. (DC).
 3. Lamp load has an inrush current of 10 times the steady-state current.
 4. Motor load has an inrush current of 6 times the steady-state current.
 5. The ratings values apply under the following test conditions:
 Ambient temperature: 20±2°C
 Ambient humidity: 65±5%
 Operating frequency: 30 operations/min

■ Characteristics

Operating speed	0.1 mm to 1 m/s (pin plunger models)
Operating frequency	Mechanical: 600 operations/min max. Electrical: 30 operations/min max.
Insulation resistance	100 MΩ min. (at 500 VDC)
Contact resistance (initial values)	D3V-21: 50 mΩ max. D3V-16, D3V-11, D3V-6: 30 mΩ max. D3V-01, 0.49 N {50 gf}: 50 mΩ max. 0.25 N {25 gf}: 100 mΩ max.
Dielectric strength (see note 2)	1,000 VAC, 50/60 Hz for 1 min between terminals of the same polarity 2,000 VAC, 50/60 Hz for 1 min between current-carrying metal parts and ground, and between each terminal and non-current-carrying metal parts
Vibration resistance (see note 3)	Malfunction: 10 to 55 Hz, 1.5-mm double amplitude
Shock resistance (see note 3)	Destruction: 400 m/s ² {approx. 40G} max. Malfunction: 100 m/s ² {approx. 10G} max.
Durability (see note 4)	Mechanical: 10,000,000 operations min. Electrical: D3V-21: 50,000 operations min. D3V-16: 100,000 operations min. D3V-11: 200,000 operations min. D3V-6, D3V-01: 500,000 operations min.
Degree of protection	IEC IP40
Degree of protection against electric shock	Class I
Proof tracking index (PTI)	250
Ambient operating temperature	D3V-21, D3V-01: -25°C to 85°C (with no icing) D3V-16, D3V-11, D3V-6: -25°C to 105°C (with no icing)
Ambient operating humidity	85% max. (for 5°C to 35°C)
Weight	Approx. 6.2 g (pin plunger models)

- Note:**
1. The data given above are initial values.
 2. The dielectric strength values shown in the table are for models with a Separator.
 3. For the pin plunger models, the above values apply for use at both the free position and total travel position. For the lever models, they apply at the total travel position.
 4. For testing conditions, contact your OMRON sales representative.

■ Approved Standards

Consult your OMRON sales representative for specific models with standard approvals.

UL1054 (File No. E41515)/CSA C22.2 No.55 (File No. LR21642)

Rated voltage	D3V-21G	D3V-16	D3V-16G	D3V-11	D3V-11G	D3V-6	D3V-6G	D3V-01
125 VAC	---	16 A, 1/2 HP	16 A, 1/2 HP	11 A, 1/2 HP	11 A, 1/2 HP	6 A, 1/4 HP	6 A, 1/4 HP	0.1 A
250 VAC	20.1 A	16 A, 1/2 HP	16 A, 1/2 HP	11 A, 1/2 HP	11 A, 1/2 HP	6 A, 1/4 HP	6 A, 1/4 HP	---
125 VDC	---	0.6 A	0.1 A	0.6 A	0.1 A	---	---	---
250 VDC	---	0.3 A	---	0.3 A	---	---	---	---

EN 61058-1: 1992+A1: 1993 (License No. 119151L)

Rated voltage	D3V-21G	D3V-16	D3V-11	D3V-6	D3V-01
125 VAC	---	---	---	---	0.1 A
250 VAC	20 (4) A	16 (3) A	11 (3) A	6 (2) A	---

Testing conditions: 5E4 (50,000 operations), T85 (0°C to 85°C) for D3V-21/D3V-01, T105 (0°C to 105°C) for D3V-16/D3V-11/D3V-6

Rated voltage	D3V-21G
250 VAC	21 (8) A

Testing conditions: 10,000 operations, T85 (0°C to 85°C)


■ Contact Specifications

Item		D3V-21	D3V-16	D3V-11	D3V-6	D3V-01
Contact	Specification	Rivet				Crossbar
	Material	Silver alloy				Gold alloy
	Gap (standard value)	0.5 mm	1 mm (F gap type) or 0.5 mm (G gap type)			1.0 mm
Inrush current	NC	50 A max.	40 A max.	24 A max.	15 A max.	---
	NO					
Minimum applicable load (see note)		160 mA at 5 VDC				1 mA at 5 VDC


Note: For more information on the minimum applicable load, refer to *Using Micro Loads* on page 109.

■ Contact Form


SPDT



SPST-NC



SPST-NO



Dimensions


■ Terminals

Note: 1. All units are in millimeters unless otherwise indicated.

2. The table below is for the SPDT contact specifications. Two terminals will be available for SPST-NO or SPST-NC contact specifications. For terminal positions, refer to the above *Contact Form*.

Terminal type	Solder Terminals(A)	Quick-connect Terminals (#187) (C2)	Quick-connect Terminals (#250) (C)
COM	Three, solder terminals	Three, quick-connect terminals (#187)	Three, quick-connect terminals (#250)
Terminal dimensions	Note: Indicates the length to the center of the 1.6-dia. holes		

■ Mounting Holes



■ Dimensions and Operating Characteristics

- Note:**
1. All units are in millimeters unless otherwise indicated.
 2. Unless otherwise specified, a tolerance of ± 0.4 mm applies to all dimensions.
 3. The following illustrations and drawings are for quick-connect terminals (#187) (terminals C2). D3V models incorporate terminals A and C. These models are different from #187 models in terminal size only. Terminals A and C are omitted from the following drawings. Refer to *Terminals* on page 101 for these terminals.
 4. The □ in the model number is for the terminal code.
 5. The Δ in the model number is for the mounting hole size.
The hole size in the following illustrations of models with a suffix "K" in the Δ is 2.9 mm.
 6. The operating characteristics are for operation in the A direction ().

Pin Plunger Models

D3V-21G-1□4A- Δ

D3V-16-1□5- Δ

D3V-11-1□5- Δ



D3V-11-1□4- Δ

D3V-6-1□4- Δ

D3V-6G-1□3- Δ

D3V-01-1□2- Δ



D3V-01-1□3- Δ



Model	D3V-21G-1□4A- Δ	D3V-16-1□5- Δ D3V-11-1□5- Δ	D3V-11-1□4- Δ D3V-6-1□4- Δ	D3V-6G-1□3- Δ	D3V-01-1□3- Δ	D3V-01-1□2- Δ
OF max.	1.23 N {125 gf}	1.96 N {200 gf}	0.98 N {100 gf}	0.49 N {50 gf}	0.49 N {50 gf}	0.25 N {25 gf}
RF min.	0.20 N {20 gf}	0.49 N {50 gf}	0.15 N {15 gf}	0.05 N {5 gf}	0.05 N {5 gf}	0.03 N {3 gf}
PT max.	1.2 mm	1.2 mm			1.2 mm	
OT min.	1.0 mm	1.0 mm			1.0 mm	
MD max.	0.3 mm	0.4 mm (F gap type) or 0.3 mm (G gap type)			0.4 mm	
OP	14.7±0.4 mm					



Short Hinge Lever Models

D3V-21G1-1□4A-Δ
D3V-161-1□5-Δ
D3V-111-1□5-Δ
D3V-111-1□4-Δ
D3V-61-1□4-Δ
D3V-6G1-1□3-Δ
D3V-011-1□3-Δ




Model	D3V-21G1-1□4A-Δ	D3V-161-1□5-Δ D3V-111-1□5-Δ	D3V-111-1□4-Δ D3V-61-1□4-Δ	D3V-6G1-1□3-Δ	D3V-011-1□3-Δ
OF max.	1.23 N {125 gf}	1.96 N {200 gf}	0.98 N {100 gf}	0.49 N {50 gf}	
RF min.	0.20 N {20 gf}	0.49 N {50 gf}	0.15 N {15 gf}	0.05 N {5 gf}	
PT max.	1.6 mm	1.6 mm			1.6 mm
OT min.	0.8 mm	0.8 mm			0.8 mm
MD max.	0.5 mm	0.6 mm (F gap type) or 0.5 mm (G gap type)			0.6 mm
OP	15.2±0.5 mm				

D3V-21G1M-1□4A-Δ
D3V-161M-1□5-Δ
D3V-111M-1□5-Δ
D3V-111M-1□4-Δ
D3V-61M-1□4-Δ
D3V-6G1M-1□3-Δ
D3V-011M-1□3-Δ



Model	D3V-21G1M-1□4A-Δ	D3V-161M-1□5-Δ D3V-111M-1□5-Δ	D3V-111M-1□4-Δ D3V-61M-1□4-Δ	D3V-6G1M-1□3-Δ	D3V-011M-1□3-Δ
OF max.	1.23 N {125 gf}	1.96 N {200 gf}	0.98 N {100 gf}	0.49 N {50 gf}	
RF min.	0.20 N {20 gf}	0.49 N {50 gf}	0.15 N {15 gf}	0.05 N {5 gf}	
PT max.	1.6 mm	1.6 mm			1.6 mm
OT min.	0.8 mm	0.8 mm			0.8 mm
MD max.	0.5 mm	0.6 mm (F gap type) or 0.5 mm (G gap type)			0.6 mm
OP	15.2±0.5 mm				

D3V-21G1K-1□4A-Δ
D3V-161K-1□5-Δ
D3V-111K-1□5-Δ
D3V-111K-1□4-Δ
D3V-61K-1□4-Δ
D3V-6G1K-1□3-Δ
D3V-011K-1□3-Δ



Model	D3V-21G1K-1□4A-Δ	D3V-161K-1□5-Δ D3V-111K-1□5-Δ	D3V-111K-1□4-Δ D3V-61K-1□4-Δ	D3V-6G1K-1□3-Δ	D3V-011K-1□3-Δ
OF max.	0.83 N {85 gf}	1.27 N {130 gf}	0.64 N {65 gf}	0.34 N {35 gf}	
RF min.	0.08 N {8 gf}	0.16 N {16 gf}	0.08 N {8 gf}	0.04 N {4 gf}	
PT max.	3.5 mm	3.5 mm			3.5 mm
OT min.	1.1 mm	1.1 mm			1.1 mm
MD max.	1.1 mm	1.2 mm (F gap type) or 1.1 mm (G gap type)			1.2 mm
OP	15.2±1.2 mm				

Hinge Lever Models

D3V-21G2-1□4A-Δ

D3V-162-1□5-Δ



D3V-112-1□5-Δ

D3V-112-1□4-Δ

D3V-62-1□4-Δ

D3V-6G2-1□3-Δ

D3V-012-1□3-Δ



Model	D3V-21G2-1□4A-Δ	D3V-162-1□5-Δ D3V-112-1□5-Δ	D3V-112-1□4-Δ D3V-62-1□4-Δ	D3V-6G2-1□3-Δ	D3V-012-1□3-Δ
OF max.	0.78 N {80 gf}	1.23 N {125 gf}	0.59 N {60 gf}		0.29 N {30 gf}
RF min.	0.06 N {6 gf}	0.14 N {14 gf}	0.06 N {6 gf}		---
PT max.	4.0 mm	4.0 mm			4.0 mm
OT min.	1.6 mm	1.6 mm			1.6 mm
MD max.	0.8 mm	1.5 mm (F gap type) or 0.8 mm (G gap type)			1.5 mm
OP	15.2±1.2 mm				

D3V-21G2M-1□4A-Δ

D3V-162M-1□5-Δ


D3V-112M-1□5-Δ

D3V-112M-1□4-Δ

D3V-62M-1□4-Δ

D3V-6G2M-1□3-Δ

D3V-012M-1□3-Δ



Model	D3V-21G2M-1□4A-Δ	D3V-162M-1□5-Δ D3V-112M-1□5-Δ	D3V-112M-1□4-Δ D3V-62M-1□4-Δ	D3V-6G2M-1□3-Δ	D3V-012M-1□3-Δ
OF max.	0.78 N {80 gf}	1.23 N {125 gf}	0.59 N {60 gf}		0.29 N {30 gf}
RF min.	0.06 N {6 gf}	0.14 N {14 gf}	0.06 N {6 gf}		---
PT max.	4.0 mm	4.0 mm			4.0 mm
OT min.	1.6 mm	1.6 mm			1.6 mm
MD max.	0.8 mm	1.5 mm (F gap type) or 0.8 mm (G gap type)			1.5 mm
OP	15.2±1.2 mm				

D3V-21G2K-1□4A-Δ

D3V-162K-1□5-Δ


D3V-112K-1□5-Δ

D3V-112K-1□4-Δ

D3V-62K-1□4-Δ

D3V-6G2K-1□3-Δ

D3V-012K-1□3-Δ



Model	D3V-21G2K-1□4A-Δ	D3V-162K-1□5-Δ D3V-112K-1□5-Δ	D3V-112K-1□4-Δ D3V-62K-1□4-Δ	D3V-6G2K-1□3-Δ	D3V-012K-1□3-Δ
OF max.	0.44 N {45 gf}	0.69 N {70 gf}	0.34 N {35 gf}	0.20 N {20 gf}	
RF min.	0.04 N {4 gf}	0.08 N {8 gf}	0.04 N {4 gf}	---	
PT max.	6.0 mm	6.0 mm			6.0 mm
OT min.	2.5 mm	2.5 mm			2.5 mm
MD max.	1.3 mm	2.0 mm (F gap type) or 1.3 mm (G gap type)			2.0 mm
OP	15.2±2.0 mm				

Long Hinge Lever Models

D3V-21G3-1□4A-Δ

D3V-163-1□5-Δ


D3V-113-1□5-Δ

D3V-113-1□4-Δ

D3V-63-1□4-Δ

D3V-6G3-1□3-Δ

D3V-013-1□3-Δ



Model	D3V-21G3-1□4A-Δ	D3V-163-1□5-Δ D3V-113-1□5-Δ	D3V-113-1□4-Δ D3V-63-1□4-Δ	D3V-6G3-1□3-Δ	D3V-013-1□3-Δ
OF max. RF min.	0.44 N {45 gf} 0.03 N {3 gf}	0.69 N {70 gf} 0.06 N {6 gf}	0.34 N {35 gf} ---	0.20 N {20 gf}	---
PT max. OT min. MD max.	9.0 mm 2.0 mm 2.0 mm	9.0 mm 2.0 mm 2.8 mm (F gap type) or 2.0 mm (G gap type)	9.0 mm 3.2 mm 2.8 mm (F gap type) or 2.0 mm (G gap type)	9.0 mm 3.2 mm 2.8 mm	9.0 mm 3.2 mm 2.8 mm
OP	15.2 ^{+2.6} _{-3.2} mm	15.2±2.6 mm			

D3V-21G3M-1□4A-Δ

D3V-163M-1□5-Δ


D3V-113M-1□5-Δ

D3V-113M-1□4-Δ

D3V-63M-1□4-Δ

D3V-6G3M-1□3-Δ

D3V-013M-1□3-Δ



Model	D3V-21G3M-1□4A-Δ	D3V-163M-1□5-Δ D3V-113M-1□5-Δ	D3V-113M-1□4-Δ D3V-63M-1□4-Δ	D3V-6G3M-1□3-Δ	D3V-013M-1□3-Δ
OF max. RF min.	0.44 N {45 gf} 0.03 N {3 gf}	0.69 N {70 gf} 0.06 N {6 gf}	0.34 N {35 gf} ---	0.20 N {20 gf}	---
PT max. OT min. MD max.	9.0 mm 2.0 mm 2.0 mm	9.0 mm 2.0 mm 2.8 mm (F gap type) or 2.0 mm (G gap type)	9.0 mm 3.2 mm 2.8 mm (F gap type) or 2.0 mm (G gap type)	9.0 mm 3.2 mm 2.8 mm	9.0 mm 3.2 mm 2.8 mm
OP	15.2 ^{+2.6} _{-3.2} mm	15.2±2.6 mm			

D3V-21G3K-1□4A-Δ

D3V-163K-1□5-Δ


D3V-113K-1□5-Δ

D3V-113K-1□4-Δ

D3V-63K-1□4-Δ

D3V-6G3K-1□3-Δ

D3V-013K-1□3-Δ



Model	D3V-21G3K-1□4A-Δ	D3V-163K-1□5-Δ D3V-113K-1□5-Δ	D3V-113K-1□4-Δ D3V-63K-1□4-Δ	D3V-6G3K-1□3-Δ	D3V-013K-1□3-Δ
OF max. RF min.	0.20 N {20 gf} ---	0.34 N {35 gf} 0.04 N {4 gf}	0.20 N {20 gf} ---	0.10 N {10 gf}	---
PT max. OT min. MD max.	15.0 mm 4.0 mm 3.0 mm	15.0 mm 4.0 mm 3.8 mm (F gap type) or 3.0 mm (G gap type)	15.0 mm 4.0 mm 3.8 mm	15.0 mm 4.0 mm 3.8 mm	15.0 mm 4.0 mm 3.8 mm
OP	15.2±3.0 mm	15.2±3.0 mm			

Simulated Roller Lever Models

D3V-21G4-1□4A-Δ

D3V-164-1□5-Δ



D3V-114-1□5-Δ

D3V-114-1□4-Δ

D3V-64-1□4-Δ

D3V-6G4-1□3-Δ

D3V-014-1□3-Δ



Model	D3V-21G4-1□4A-Δ	D3V-164-1□5-Δ D3V-114-1□5-Δ	D3V-114-1□4-Δ D3V-64-1□4-Δ	D3V-6G4-1□3-Δ	D3V-014-1□3-Δ
OF max. RF min.	0.83 N {85 gf} 0.07 N {7 gf}	1.23 N {125 gf} 0.14 N {14 gf}	0.59 N {60 gf} 0.06 N {6 gf}	0.29 N {30 gf} ---	
PT max. OT min. MD max.	4.0 mm 1.6 mm 1.4 mm	4.0 mm 1.6 mm 1.5 mm (F gap type) or 0.8 mm (G gap type)			4.0 mm 1.6 mm 1.5 mm
OP	18.7±1.2 mm				

D3V-21G4M-1□4A-Δ

D3V-164M-1□5-Δ


D3V-114M-1□5-Δ

D3V-114M-1□4-Δ

D3V-64M-1□4-Δ

D3V-6G4M-1□3-Δ

D3V-014M-1□3-Δ



Model	D3V-21G4M-1□4A-Δ	D3V-164M-1□5-Δ D3V-114M-1□5-Δ	D3V-114M-1□4-Δ D3V-64M-1□4-Δ	D3V-6G4M-1□3-Δ	D3V-014M-1□3-Δ
OF max.	0.83 N {85 gf}	1.23 N {125 gf}	0.59 N {60 gf}	0.29 N {30 gf}	
RF min.	0.07 N {7 gf}	0.14 N {14 gf}	0.06 N {6 gf}	---	
PT max.	4.0 mm	4.0 mm			4.0 mm
OT min.	1.6 mm	1.6 mm			1.6 mm
MD max.	1.4 mm	1.5 mm (F gap type) or 0.8 mm (G gap type)			1.5 mm
OP	18.7±1.2 mm				

D3V-21G4K-1□4A-Δ

D3V-164K-1□5-Δ


D3V-114K-1□5-Δ

D3V-114K-1□4-Δ

D3V-64K-1□4-Δ

D3V-6G4K-1□3-Δ

D3V-014K-1□3-Δ



Model	D3V-21G4K-1□4A-Δ	D3V-164K-1□5-Δ D3V-114K-1□5-Δ	D3V-114K-1□4-Δ D3V-64K-1□4-Δ	D3V-6G4K-1□3-Δ	D3V-014K-1□3-Δ
OF max. RF min.	0.54 N {55 gf} 0.03 N {3 gf}	0.74 N {75 gf} 0.10 N {10 gf}	0.39 N {40 gf} 0.03 N {3 gf}	0.20 N {20 gf} ---	
PT max. OT min. MD max.	8.0 mm 1.5 mm 3.0 mm	8.0 mm 1.5 mm 3.5 mm (F gap type) or 3.0 mm (G gap type)			8.0 mm 1.5 mm 3.5 mm
OP	18.7±1.2 mm				

Short Hinge Roller Lever Models

D3V-21G5-1□4A-Δ

D3V-165-1□5-Δ



D3V-115-1□5-Δ

D3V-115-1□4-Δ

D3V-65-1□4-Δ

D3V-6G5-1□3-Δ

D3V-015-1□3-Δ



Model	D3V-21G5-1□4A-Δ	D3V-165-1□5-Δ D3V-115-1□5-Δ	D3V-115-1□4-Δ D3V-65-1□4-Δ	D3V-6G5-1□3-Δ	D3V-015-1□3-Δ
OF max. RF min.	1.42 N {145 gf} 0.2 N {20 gf}	2.35 N {240 gf} 0.49 N {50 gf}	1.18 N {120 gf} 0.15 N {15 gf}	0.59 N {60 gf} 0.06 N {6 gf}	
PT max. OT min. MD max.	1.6 mm 0.8 mm 0.5 mm	1.6 mm 0.8 mm 0.6 mm (F gap type) or 0.5 mm (G gap type)			1.6 mm 0.8 mm 0.6 mm
OP	20.7±0.6 mm				

D3V-21G5M-1□4A-Δ

D3V-165M-1□5-Δ


D3V-115M-1□5-Δ

D3V-115M-1□4-Δ

D3V-65M-1□4-Δ

D3V-6G5M-1□3-Δ

D3V-015M-1□3-Δ



Model	D3V-21G5M-1□4A-Δ	D3V-165M-1□5-Δ D3V-115M-1□5-Δ	D3V-115M-1□4-Δ D3V-65M-1□4-Δ	D3V-6G5M-1□3-Δ	D3V-015M-1□3-Δ
OF max. RF min.	1.42 N {145 gf} 0.2 N {20 gf}	2.35 N {240 gf} 0.49 N {50 gf}	1.18 N {120 gf} 0.15 N {15 gf}	0.59 N {60 gf} 0.06 N {6 gf}	
PT max. OT min. MD max.	1.6 mm 0.8 mm 0.5 mm	1.6 mm 0.8 mm 0.6 mm (F gap type) or 0.5 mm (G gap type)			1.6 mm 0.8 mm 0.6 mm
OP	20.7±0.6 mm				

D3V-21G5K-1□4A-Δ

D3V-165K-1□5-Δ



D3V-115K-1□5-Δ

D3V-115K-1□4-Δ

D3V-65K-1□4-Δ

D3V-6G5K-1□3-Δ

D3V-015K-1□3-Δ



Model	D3V-21G5K-1□4A-Δ	D3V-165K-1□5-Δ D3V-115K-1□5-Δ	D3V-115K-1□4-Δ D3V-65K-1□4-Δ	D3V-6G5K-1□3-Δ	D3V-015K-1□3-Δ
OF max. RF min.	0.98 N {100 gf} 0.08 N {8 gf}	1.57 N {160 gf} 0.15 N {15 gf}	0.78 N {80 gf} 0.08 N {8 gf}	0.39 N {40 gf} 0.04 N {4 gf}	
PT max. OT min. MD max.	2.6 mm 1.0 mm 0.8 mm	2.6 mm 1.0 mm 0.9 mm (F gap type) or 0.8 mm (G gap type)			2.6 mm 1.0 mm 0.9 mm
OP	20.7±1.0 mm				

Hinge Roller Lever Models

D3V-21G6-1□4A-Δ

D3V-166-1□5-Δ


D3V-116-1□5-Δ

D3V-116-1□4-Δ

D3V-66-1□4-Δ

D3V-6G6-1□3-Δ

D3V-016-1□3-Δ



Model	D3V-21G6-1□4A-Δ	D3V-166-1□5-Δ D3V-116-1□5-Δ	D3V-116-1□4-Δ D3V-66-1□4-Δ	D3V-6G6-1□3-Δ	D3V-016-1□3-Δ	
OF max.	0.79 N {80 gf}	1.23 N {125 gf}	0.59 N {60 gf}	0.29 N {30 gf}		
RF min.	0.05 N {5 gf}	0.14 N {14 gf}	0.06 N {6 gf}	---		
PT max.	4.0 mm	4.0 mm	1.5 mm (F gap type) or 0.8 mm (G gap type)			
OT min.	1.6 mm	1.6 mm				4.0 mm
MD max.	0.8 mm	1.5 mm (F gap type) or 0.8 mm (G gap type)				1.6 mm
OP	20.7±1.2 mm					

D3V-21G6M-1□4A-Δ

D3V-166M-1□5-Δ


D3V-116M-1□5-Δ

D3V-116M-1□4-Δ

D3V-66M-1□4-Δ

D3V-6G6M-1□3-Δ

D3V-016M-1□3-Δ



Model	D3V-21G6M-1□4A-Δ	D3V-166M-1□5-Δ D3V-116M-1□5-Δ	D3V-116M-1□4-Δ D3V-66M-1□4-Δ	D3V-6G6M-1□3-Δ	D3V-016M-1□3-Δ	
OF max.	0.79 N {80 gf}	1.23 N {125 gf}	0.59 N {60 gf}	0.29 N {30 gf}		
RF min.	0.05 N {5 gf}	0.14 N {14 gf}	0.06 N {6 gf}	---		
PT max.	4.0 mm	4.0 mm	1.5 mm (F gap type) or 0.8 mm (G gap type)			
OT min.	1.6 mm	1.6 mm				4.0 mm
MD max.	0.8 mm					1.6 mm
OP	20.7±1.2 mm					
	1.5 mm					

D3V-21G6K-1□4A-Δ

D3V-166K-1□5-Δ


D3V-116K-1□5-Δ

D3V-116K-1□4-Δ

D3V-66K-1□4-Δ

D3V-6G6K-1□3-Δ

D3V-016K-1□3-Δ



Model	D3V-21G6K-1□4A-Δ	D3V-166K-1□5-Δ D3V-116K-1□5-Δ	D3V-116K-1□4-Δ D3V-66K-1□4-Δ	D3V-6G6K-1□3-Δ	D3V-016K-1□3-Δ
OF max.	0.49 N {50 gf}	0.74 N {75 gf}	0.39 N {40 gf}	0.20 N {20 gf}	
RF min.	0.03 N {3 gf}	0.10 N {10 gf}	0.03 N {3 gf}	---	
PT max.	7.2 mm	7.2 mm			7.2 mm
OT min.	2.0 mm	2.0 mm			2.0 mm
MD max.	2.0 mm	2.7 mm (F gap type) or 2.0 mm (G gap type)			2.7 mm
OP	20.7±2.2 mm				

Precautions

■ Cautions

Handling

Be careful not to drop the switch. Doing so may cause damage to the switch's internal components because it is designed for a small load.

■ Correct Use

Mounting

Use two M3 mounting screws with an appropriate screwdriver to mount the switch. Tighten the screws to a torque of 0.39 to 0.59 N • m {4 to 6 kgf • cm}.

Mounting Direction

Mount lever-operated switches with a maximum operating force of 0.49 N in a direction where the actuator weight will not be applied to the switch. Since the switch is designed for a small load, its resetting force is small. Therefore, resetting failure may occur if unnecessary load is applied to the switch.


Insulation Distance

According to EN61058-1, the minimum insulation thickness for this switch should be 1.1 mm and minimum clearance distance between the terminal and mounting plate should be 1.9 mm. If the insulation distance cannot be provided in the product incorporating the switch, either use a switch with insulation barrier or use a Separator to ensure sufficient insulation distance.

Using Micro Loads

Using a model for ordinary loads to open or close the contact of a micro load circuit may result faulty contact. Use models that operate in the following range. However, even when using micro load models within the operating range shown below, if inrush current occurs when the contact is opened or closed, it may increase contact wear and so decrease durability. Therefore, insert a contact protection circuit where necessary.

The minimum applicable load is the N-level reference value. This value indicates the malfunction reference level for the reliability level of 60% ($\lambda 60$). The equation, $\lambda 60 = 0.5 \times 10^{-6}/\text{operations}$ indicates that the estimated malfunction rate is less than 1/2,000,000 operations with a reliability level of 60%.



Solder Terminal Approval Conditions

Soldering iron can be used.
Soldering hook hole available.
Soldering terminal types 1 and 2 are met.

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.