G3VM-62C1/F1 MOS FET Relays

Analog-switching MOS FET Relays for High Switching Currents, with Dielectric Strength of 2.5 kVAC between I/O.

• New 2-channel model included in the 60-V load voltage series.


- Switches minute analog signals.
- Dielectric strength of 2,500 Vrms between I/O.
- Surface-mounting models included in series.

RoHS compliant


■ Application Examples

- Test & Measurement equipment
- Security equipment

ennica szi



Terminal Arrangement/Internal Connections



Note: The actual product is marked differently from the image shown here.

■ List of Models

Package type	Contact form	Terminals	Load voltage	Model	Minimum package quantity	
	Contact Ionni	Terminais	(peak value) *	Model	Number per tube	Number per tape and reel
DIP8	2a (DPST-NO)	PCB Terminals		G3VM-62C1	50	50 -
		Surface-mounting Terminals	60 V	G3VM-62F1	50	
	(81 01 110)	Sunace-mounting reminals		G3VM-62F1(TR)	-	1,500

* The AC peak and DC value are given for the load voltage.


■ Absolute Maximum Ratings (Ta = 25°C)

	Item	Symbol	Rating	Unit	Measurement conditions		
	LED forward current	lF	50	mA			
τ	Repetitive peak LED forward current	IFP	1	Α	100 µs pulses, 100 pps		
ā	LED forward current reduction rate	∆IF/°C	-0.5	mA/°C	Ta ≥ 25°C		
<u>-</u>	LED reverse voltage	VR	5	V			
	Connection temperature	TJ	125	°C			
÷	Load voltage (AC peak/DC)	Voff	60	V			
	Continuous load current (AC peak/DC)	lo	500	mA			
ont	ON current reduction rate	∆lo/°C	-5.0	mA/°C	Ta≥25°C		
	Connection temperature	TJ	125	°C			
Dielectric strength between I/O (See note 1.)		VI-0	2500	Vrms	AC for 1 min	Note: 1. The dielectric strength between the inpu	
Ambient operating temperature		Та	-40 to +85	°C	With no icing or condensation	output was checked by applying volta between all pins as a group on the LEI	
Ambient storage temperature		Tstg	-55 to +125	°C	With no icing or condensation		
Soldering temperature		-	260	°C	10 s	all pins as a group on the light-receiving	

Electrical Characteristics (Ta = 25°C)

Item		Symbol	Minimum	Typical	Maximum	Unit	Measurement conditions	
	LED forward voltage	VF	1.0	1.15	1.3	V	IF = 10 mA	
Input	Reverse current	IR	-	-	10	μA	VR = 5 V	N
	Capacity between terminals	Ст	-	30	-	pF	V = 0, f = 1 MHz	
	Trigger LED forward current	IFT	-	1.6	3	mA	lo = 500 mA	1
Output	Maximum resistance with output ON	Ron	-	1.0	2.0	Ω	IF = 5 mA, Io = 500 mA	1
	Current leakage when the relay is open	ILEAK	-	-	1.0	μA	Voff = 60 V	1
	Capacity between terminals	COFF	-	130	-	pF	V = 0, f = 1 MHz	1
Capacity between I/O terminals		CI-0	-	0.8	-	pF	f = 1 MHz, Vs = 0 V	1
Insulation resistance between I/O terminals		RI-0	1000	-	-	MΩ	VI-0 = 500 VDC, RoH \leq 60%	1
Turn-ON time		ton	-	0.8	2.0	ms	$I_F = 5 \text{ mA}, \text{ RL} = 200 \Omega,$	1
Turn-OFF time		toff	-	0.1	0.5	ms	VDD = 20 V(See note 2.)	

lote: 2. Turn-ON and Turn-OFF Times



91

G3VM-62C1/F1


Recommended Operating Conditions

Use the G3VM under the following conditions so that the Relay will operate properly.


Item	Symbol	Minimum	Typical	Maximum	Unit
Load voltage (AC peak/DC)	Vdd	-	-	48	V
Operating LED forward current	lF	5	7.5	25	mA
Continuous load current (AC peak/DC)	lo	-	-	500	mA
Ambient operating temperature	Та	-20	-	65	°C

Engineering Data


LED forward current vs. Ambient temperature




Continuous load current vs. Ambient temperature




LED forward current vs. LED forward voltage




Continuous load current vs. On-state voltage




Turn ON, Turn OFF time vs. LED forward current




On-state resistance vs. Ambient temperature




Turn ON, Turn OFF time vs. Ambient temperature



Trigger LED forward current vs. Ambient temperature



Current leakage vs. Ambient temperature




■ Safety Precautions

• Refer to "Common Precautions" for all G3VM models.

■ Appearance


DIP (Dual Inline Package) DIP8



Note: The actual product is marked differently from the image shown here.

Dimensions

(Unit:mm)



Application examples provided in this document are for reference only. In actual applications, confirm equipment functions and safety before using the product.
Consult your OMRON representative before using the product under conditions which are not described in the manual or applying the product to nuclear control systems, railroad systems, aviation systems, vehicles, combustion systems, medical equipment, amusement machines, safety equipment, and other systems or equipment that may have a serious influence on lives and property if used improperly. Make sure that the ratings and performance characteristics of the product provide a margin of safety for the system or equipment, and be sure to provide the system or equipment with double safety mechanisms.

Note: Do not use this document to operate the Unit.

OMRON Corporation ELECTRONIC AND MECHANICAL COMPONENTS COMPANY C

Contact: www.omron.com/ecb

Cat. No. K145-E1-01 0412(0412)(O)